

CORNER TEE ROSETTES—2 ELEMENT 90°

MOST POPULAR MODELS HIGHLIGHTED!



To Order (Specify Model Number)

Custom-Designed Strain Gages Available!
No Minimum Quantities.
Consult Engineering.

Custom-Designed Strain Gages Available! Minimum Quantities. Consult Engineering.		MODEL NO.	PRICE PER PKG OF 5	NOM. RESIS- TANCE (Ω)	DIMENSIONS mm (in) [†]				MAX PERMITTED BRIDGE ENERGIZING VOLTAGE (Vrms)	TERMINATION	TEMP COMP	TERM PAD
					GRID		CARRIER					
					A	B	C	D				
Shown actual size, 9.3 mm  Leads not shown	SGD-1/120-RYB21	\$72.60	120	1.6 (0.063)	1.7 (0.067)	9.3 (0.37)	9.3 (0.37)	3	Ribbon Leads	ST	BTP-1	
	SGD-1/120-RYB23	72.60	120					4	Ribbon Leads	AL		
	SGD-1/120-RYB81	54.60	120					3	Solder Pads	ST		
	SGD-1/120-RYB83	54.60	120					4	Solder Pads	AL		
Shown actual size, 9.3 mm  Leads not shown	SGD-1/350-RYB21	\$72.60	350	1.6 (0.063)	2.1 (0.083)	9.3 (0.37)	9.3 (0.37)	6	Ribbon Leads	ST	BTP-1	
	SGD-1/350-RYB23	72.60	350					8.5	Ribbon Leads	AL		
	SGD-1/350-RYB81	54.60	350					6	Solder Pads	ST		
	SGD-1/350-RYB83	54.60	350					8.5	Solder Pads	AL		
Shown actual size, 11 mm  Leads not shown	SGD-3/120-RYB21	\$76.80	120	3.0 (0.118)	1.7 (0.067)	11.0 (0.43)	11.0 (0.43)	4.5	Ribbon Leads	ST	BTP-2	
	SGD-3/120-RYB23	76.80	120					6	Ribbon Leads	AL		
	SGD-3/120-RYB81	58.80	120					4.5	Solder Pads	ST		
	SGD-3/120-RYB83	58.80	120					6	Solder Pads	AL		
Shown actual size, 11 mm  Leads not shown	SGD-3/350-RYB21	\$76.80	350	3.0 (0.118)	2.1 (0.083)	11.0 (0.43)	11.0 (0.43)	8.5	Ribbon Leads	ST	BTP-3	
	SGD-3/350-RYB23	76.80	350					12	Ribbon Leads	AL		
	SGD-3/350-RYB81	58.80	350					8.5	Solder Pads	ST		
	SGD-3/350-RYB83	58.80	350					12	Solder Pads	AL		
Shown actual size, 16.3 mm  Leads not shown	SGD-6/120-RYB21	\$88.20	120	6.0 (0.236)	3.2 (0.126)	16.3 (0.64)	16.3 (0.64)	8.5	Ribbon Leads	ST	BTP-4	
	SGD-6/120-RYB23	88.20	120					12	Ribbon Leads	AL		
	SGD-6/120-RYB81	70.20	120					8.5	Solder Pads	ST		
	SGD-6/120-RYB83	70.20	120					12	Solder Pads	AL		
Shown actual size, 16.3 mm  Leads not shown	SGD-6/350-RYB21	\$88.20	350	6.0 (0.236)	3.1 (0.122)	16.3 (0.64)	16.3 (0.64)	14	Ribbon Leads	ST	BTP-4	
	SGD-6/350-RYB23	88.20	350					20	Ribbon Leads	AL		
	SGD-6/350-RYB81	70.20	350					14	Solder Pads	ST		
	SGD-6/350-RYB83	70.20	350					20	Solder Pads	AL		

DISCOUNT SCHEDULE

1 to 10 pkgs	Net
11 to 24 pkgs	.5%
25 to 49 pkgs	.10%
50 and up and OEM	Consult Factory

[†] For dimensions key, see page 15.

Note: For strain gage accessories see pages 59 to 61.

Ordering Example: SGD-1/120-RYB83,

120 Ω nominal-resistance strain gage, \$54.60.

NOTE

ST = Steel
AL = Aluminum

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters