



EMI Protection Hardware with Nickel-Zinc Ferrite Cores

Cable Clamps for **Standard** and **Miniature** Connectors




See Section I
for analab Services



Ferrite Cable Clamp, Model PCLM-FT (\$2.50), Attaches to Standard Connectors to Provide EMI Protection



EMI/RFI Problems?
& analab® Can Help!
Complete EMC and FCC Compliance Testing and Technical Assistance. For Complete Information See Section I



Twisted Shielded Wire See Page, H-36.

FERRITE CORE INCLUDED

PATENTED

Covered by U.S and International patents and pending applications

Ferrite Cable Clamp

ALL MODELS AVAILABLE FOR FAST DELIVERY!

Model No.	Price Each	Compatible Connectors (By Type)	Max Wire Gage for Duplex Wire	Impedance (ohms) @ ±20%		Description
				@25 Mhz	@100 Mhz	
PCLM-FT (for Standard Connectors)	\$2.50	OST, OSTW, HST, HSTW, OGP, GST, HGST, OTP	14 AWG	120	225	Ferrite Cable Clamp Standard Size
PCLM-SMP-FT (for Miniature Connectors)	2.50	SMP, SMPW, GMP, HGMP, HMP, HMPW, MTP	22 AWG	105	155	Ferrite Cable Clamp, Miniature Size
PCLM-SMP-RSC-FT (for Miniature Connectors)	2.50	SMP, SMPW, GMP, HGMP, HMP, HMPW, MTP	22 AWG	105	155	Ferrite Cable Clamp, Miniature Size Use with RSC Cable

Ordering Example: PCLM-SMP-FT, ferrite cable clamp for subminiature connector, \$2.50 ea.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters