

# Thermistor Probes

Series "400"  
For Use with  
Heavy-Duty  
HDX Handle



Aluminum die-cast handle.

Retractable cable.

HDX-OST Series Handle

**\$37<sup>50</sup>**

(Probe not included)


The OMEGA® HDX handle must have an uncompensated OST connector and copper extension cord. For use with thermistor probes. See page A-127.



**General Purpose Probe**

THX-400-GP-12\*  
Starts at  
**\$70**

The THX-400-GP probe used with an HDX handle is ideal for general purpose immersion measurement in gases and liquids. Made from a rugged 3.0 mm ( $\frac{1}{8}$ " O.D. 304 stainless steel sheath 300 mm (12") long, the probe will adapt to most process applications. A high precision 44033 thermistor element is used ( $2252 \Omega @ 25^\circ\text{C}/75^\circ\text{F}$ ), which provides  $0.1^\circ\text{C}/\text{F}$  interchangeability and a temperature range of  $-40$  to  $100^\circ\text{C}$  ( $-40$  to  $212^\circ\text{F}$ ).



**Air Probe**

THX-400-AP-12\*  
Starts at  
**\$90**

The THX-400-AP is designed for HVAC applications. The small diameter sheath and radiant energy shield easily fit into duct work, grilles and vents. The probe will work with the OMEGA® HDX handle or can be permanently mounted using OMEGALOK® compression fittings. Made from a rugged 4.8 mm ( $\frac{3}{16}$ " O.D. 304 stainless steel sheath 300 mm (12") long, the tip is perforated to expose the thermistor bead to air flow for fast, accurate measurements. The 44033 precision thermistor element is rated up to  $100^\circ\text{C}$  ( $212^\circ\text{F}$ ).



**Penetration Probe**

THX-400-NP-12\*  
Starts at  
**\$80**

The THX-400-NP probe used with an HDX handle will easily pierce soft and semi-frozen material as well as soil and sand. Made from a rugged 3.1 mm ( $\frac{1}{8}$ " O.D. 304 stainless steel sheath 300 mm (12") long. A high precision 44033 thermistor element is used which provides  $0.1^\circ\text{C}/\text{F}$  interchangeability and a temperature range of  $-40$  to  $100^\circ\text{C}$  ( $-40$  to  $212^\circ\text{F}$ ).

**SPECIAL ASSEMBLIES AVAILABLE!**

\*Other thermistor elements, sheath lengths and configurations are available upon request. See Section I or consult Custom Engineering for quotation.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters