



Models IC11A-F and IC11-PLUS Miniature Interface Converters

\$89

Basic Unit



- ✓ Connect Directly to 9-Pin Serial Port
- ✓ Miniature Size Conserves Space
- ✓ Model IC11-PLUS Has Automatic Data Direction Control Circuit

OMEGA's miniature IC11 converters provides all the features required of high quality interface converters in a miniature package and at a low cost!

The IC11 intelligent RS-232 to RS-422/485 converter can be selected for half/full duplex, and will allow transmission distances of up to 1220 m (4000').

The IC11 converts an RS-232 signal to RS-422/485. Simply attach one end to an RS-232 device and connect the other end (screw terminals) to an RS-422/485 device.

The converter allows data transfer rates up to 120 Kbps. Power is acquired directly from a computer's serial port, or using the included USB-plug cable.

Specifications

Function:

RS-232 to RS-422/485 converter


Power:

From RS-232 port or external 5 V power from included USB-plug cable

Transmission: Asynchronous

Operate Mode: Full/half duplex

Data Rate: Up to 120 Kbps



IC11A-F, \$89, shown smaller than actual size

IC11-PLUS, \$128, shown smaller than actual size

IC11A-F Transmitter/Receiver Control

- 1) TX Enabled and RX Enabled
- 2) TX Enabled when RTS is ON, RX Enabled
- 3) TX Enabled when RTS ON, RX Enabled when RTS OFF

IC11-PLUS Transmitter/Receiver Control:

Automatic

Communication Mode:

IC11A-F: DTE/DCE;

IC11-PLUS: DCE only

Connector: DB25F (includes DB-25M/DB-9F mini-gender changer)

RS422/485 Connector: 5 screw terminals

Dimensions:

69 mm L x 53 mm W x 22 mm H (2.7 x 2.1 x 0.9")

Environmental:

0 to 50°C (32 to 122°F),
0 to 90% RH

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model	Price	Description
IC11A-F	\$89	RS-232 to RS-422/485 miniature interface converter
IC11-PLUS	128	RS-232 TO RS422/485 miniature interface converter with auto direction control circuit

Each unit supplied with 1.5 m (5') USB-plug cable, DB-25M/DB-9F mini-gender changer and complete operator's manual.

Ordering Example: IC11A-F, RS-232 to RS-422/485 mini interface converter, \$89.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters