

OMA-VM500-3

OMEGAPHONE® Automatic Temperature Alarm Dialer

\$260
Basic Unit



- ✓ Monitors Temperature and Power Status
- ✓ Programmable High and Low Limits for Temperature
- ✓ Program up to Four 20 Digit Phone Numbers
- ✓ Works with Telephone Pagers
- ✓ Easy-to-Follow Menu Driven Programming Done Over the Phone

Model OMA-VM500-3 is a full-featured monitor and alarm system that monitors temperature and power status wherever the unit is located. This system can dial up to four phone numbers, and the integrated voice tells you the temperature and whether the power is on or how long the power has been off. You can also call the unit at anytime and hear a status report that gives you an update on the conditions at your facility.

The OMA-VM500-3 is easily programmed over the phone. Simply locate the unit in the area where you want to measure the temperature. Plug in the phone line and the power adapter and turn the unit on. Call the unit from another phone or cell phone and follow the spoken instructions to program the temperature limits and the emergency phone numbers. The system is now programmed and is monitoring temperature and power at your facility.

Specifications

Temperature Measurement


Range: 32 to 125°F (0 to 52°C); unit is set up factory default for Fahrenheit operation (can be changed in the field for Celsius operation)

Temperature Sensor: Solid state

Accuracy: $\pm 2^\circ\text{F}$

High and Low Programmable

Temperature Limits: 35 to 125°F



OMA-VM500-3, \$260, shown smaller than actual size

Operating Ambient:

0 to 52°C (32 to 125°F)

Telephone: Standard RJ11 phone jack connection

Telephone Numbers: Stores up to four phone numbers up to 20 digits long

Personal Identification Message: Record up to a 10-second message over the phone

Operation: Operates with answering machine on the same phone line

Power: Powered from included 120 Vac wall mount transformer power supply

Battery Backup: 4 hour rechargeable battery backup; 20 or 30 hours optional

Dimensions:

140 mm H x 127 mm W x 64 mm D (5.5 x 5 x 2.5")

Material: ABS plastic

Weight: 0.45 kg (1 lb)

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model Number	Price	Description
OMA-VM500-3	\$260	Automatic temperature alarm dialer
OMA-VM500-3-B20	305	Temperature alarm dialer with 20-hour battery backup
OMA-VM500-3-B30	325	Temperature alarm dialer with 30-hour battery backup

Each unit is supplied with complete user's manual.

Ordering Example: OMA-VM500-3-B20 automatic temperature alarm dialer with 20-hour battery backup and OMEGACARE™ 1-year extended warranty for OMA-VM500-3-B20 (adds 1 year to standard 1-year warranty), \$305 + 30 = \$335.



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters