



CONDUCTIVITY INSTRUMENTS

5-Range Portable Analog Conductivity Meters

CDH-37
\$390



Electronics Only

- ✓ 5 Ranges from 0 to 2 $\mu\text{mho/cm}$ to 0 to 20,000 $\mu\text{mho/cm}$
- ✓ Ideal for Most Water Applications



The CDH-37 portable conductivity meter provides excellent cost-effective performance in a field unit that measures ionized materials in solution. Housed in a rugged, high density polyethylene protective case, the CDH-37 includes a break-resistant probe with an internal thermistor for automatic temperature compensation. The unit features 5 conductivity ranges from 0 to 2 $\mu\text{mho/cm}$ to 0 to 20,000 $\mu\text{mho/cm}$, to cover most water applications. To ensure versatility, the CDH-37 operates on 8 AA batteries and comes complete with probe and standard solutions.

Unit supplied as a complete kit. Includes meter built into rugged carrying case, conductivity cell, conductivity standard solutions, complete operator's manual and 8 "AA" batteries.

CDH-37, \$390, shown smaller than actual size.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
CDH-37	\$390	Portable conductivity kit
CDE-37-R	148	Replacement conductivity cell with 1.8 m (6') of cable

Specifications

Readout: 152.4 mm (6") analog meter
Ranges: 0 to 2 $\mu\text{mho/cm}$, 0 to 20 $\mu\text{mho/cm}$, 0 to 200 $\mu\text{mho/cm}$, 0 to 2000 $\mu\text{mho/cm}$, 0 to 20,000 $\mu\text{mho/cm}$
Accuracy: $\pm 2\%$ full scale
Temperature Compensation: Auto, 5 to 45°C (41 to 113°F)
Sensor: DIP type with 1.8 m (6') of cable
Power: 8 "AA" batteries (included)
Size: 315 x 108 x 203 mm (12.4 x 4.3 x 8.0")
Weight: 1.8 kg (3.96 lb)

Accessories Calibration Solutions

Model No.	Price	Description
CDSA-45	\$10/qt	Conductivity solutions 45 $\mu\text{mho/cm}$ (μS)
CDSA-450	10/qt	Conductivity solutions 450 $\mu\text{mho/cm}$ (μS)
CDSA-1500	10/qt	Conductivity solutions 1500 $\mu\text{mho/cm}$ (μS)
CDSA-4500	10/qt	Conductivity solutions 4500 $\mu\text{mho/cm}$ (μS)
OP-20	79	Reference Book: Calibration, a Technician's Guide 2005

Ordering Examples: CDH-37, conductivity kit, and CDE-37-R, replacement cell, \$390 + 148 = \$538.
 CDH-37, conductivity kit, and CDSA-1500, conductivity solution, \$390 + 10 = \$400.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters