

HEAVY DUTY, ELECTRONIC DRAIN VALVE

FSV-ADV Series
Starts at

\$129



- ✓ 100% Continuous Duty Cycle
- ✓ NEMA 4 (IP65)
- ✓ Strainer Ball Valve Included
- ✓ Carpenter 18 FM Stainless Steel Operator
- ✓ LED to Indicate Electrical Power is On
- ✓ LED to Indicate Valve Is Open

OMEGA's FSV-ADV high quality, price competitive systems offer a cost-effective means of removing condensate from compressors, receivers, after coolers, drip legs and dryers. Each is supplied standard with a 1.8 m (6') heavy duty cable with grounded 115 Vac plug and strainer ball valve. The TEST button allows manual override to confirm valve on/off function.

SPECIFICATIONS

Mounting Position: Any

ON Time: Adjustable 0.5 to 10 seconds

OFF Time: Adjustable 0.5 to 45 minutes

Power: 115 Vac, 60 Hz

Wetted Parts:

Brass, Carpenter 18 FM SS, FKM

Power: 18 W holding,
36 W inrush (12 W holding,
24 W inrush for FSV-ADV10)

Shipping Weight: 1.13 kg (2.5 lb)

Min/Max Temperature: 1 to 129°C
(35 to 265°F)



FSV-ADV25, \$159, shown larger than actual size.



Strainer ball valve, included, can be cleaned without tools.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)					
Model No.	Price	Valve Port Size	Pressure Range (psig)	Discharge Volume Per 5-Second "On" Time (gal)*	Dimensions H x W x D mm (in)
FSV-ADV10	\$129	1/4"	0 to 300	0.11	102 x 45 x 89 (4 x 1.75 x 3.5)
FSV-ADV25	159	1/4"	2 to 300	1.38	102 x 45 x 89 (4 x 1.75 x 3.5)
FSV-ADV38	159	3/8"	2 to 300	1.54	108 x 45 x 89 (4.25 x 1.75 x 3.5)
FSV-ADV50	159	1/2"	2 to 300	1.77	108 x 45 x 89 (4.25 x 1.75 x 3.5)

* When used with 90 psi compressed air system.

Accessory

Model No.	Price	Description
FW-346	\$99	Reference Book: Control Valve Primer

Comes complete with strainer ball valve and operator's manual.

Ordering Examples: FSV-ADV50, electronic drain valve, 1/2" port size, \$159.

FSV-ADV25, electronic drain valve, 1/4" port size, \$159.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters