



Handheld Fruit and Vegetable Ripeness/Hardness Tester

HFH80 Series



The HFH80 Series Ripeness/Hardness Tester is a handheld compact penetrometer for fruit firmness and some vegetable hardness testing, the universally accepted measure of ripeness. This tester is the growers' indispensable tool for knowing when to pick and ship. The HFH80 Series fruit tester measures the force required to push a plunger tip of specified size into the fruit pulp. The force reading assists in determining the appropriate picking time or monitoring fruit softening during storage. Because of the number of fruit and vegetable varieties, geographical locations and other variations, the appropriate firmness for harvesting will vary. User must combine experience and expertise to establish the firmness value that applies to their specific variety and locale.

Specifications

Operating Conditions

Temperature: 0 to 45°C (32 to 113°F)

Humidity: Below 90% RH

Dimensions: 204 H x 62 W x 33 mm D (8.0 x 2.4 x 1.3")

Weight: 230 g (8.1 oz) (not including batteries)

Display: 4-digits, 10 mm (0.4") LCD

Ranges:

HFH81: 0.2 to 5.0 kgf/cm, tip size 3.5 mm (0.14")

HFH83: 0.2 to 11.0 kgf/cm², tip size 11.1 mm (0.4")

0.4 to 22.0 kgf/cm², tip size 7.9 mm (0.3")

Resolution:

0.01 if reading <10

0.1 if 10 <reading <99.9

1 if reading >100

Unit Conversion:

kgf (kgf/cm²)

lbf (lbf/cm²)

N (N/cm²)

Pa

Accuracy: ±(1%H+0.1)

kgf/cm²

Power Supply:

4 x 1.5V "AAA" batteries (included)



HFH81, fruit hardness tester.

To Order Visit omega.com/hfh80 for Pricing and Details

Model No.	Description
HFH81	Fruit hardness tester, small fruits, soft fruits
HFH83	Fruit hardness tester, large fruits, firm/hard fruits
MN1500-4	Replacement "AAA" batteries (4)

Comes complete with digital meter, plunger tips, (4) 1.5V "AAA" batteries, operator's manual, and carrying case. Communication cable and software comes with HFH83 only.

Ordering Example: HFH81, fruit hardness tester for small fruits.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters