

# REFRIGERANT LEAK DETECTOR



LDH-380  
**£113**



- ✓ Microprocessor Control with Advanced Digital Signal Processing
- ✓ Multi-Color Visual Display
- ✓ High-Low Leak Sensitivity Selector
- ✓ Low-Battery Indication
- ✓ Semiconductor Gas Sensor
- ✓ Detection of R-134A, R-410A, R-407C and R22 Freon Gases
- ✓ Carrying Case Included
- ✓ 39 cm (15") Flexible Stainless Steel Probe
- ✓ Reference Leak Source Included
- ✓ Ambient Concentration Reset

The LDH-380 refrigerant leakage detector is the perfect tool for maintaining the air-condition or a cooling system with compressor and refrigerant. This unit uses a newly developed semi-conductor sensor which is extremely sensitive to variety of general refrigerants.

## SPECIFICATIONS

**Detectable Gases:** R-134A, R-404A, R-407C, R-410A, R-22, etc.  
**Sensitivity H L:** R-22, 134A 6g/year 30g/year; R-404A, 407C, 410A 8g/year 40g/year  
**Alarm Method:** Buzzer, tri-color LED bar indicator  
**Power Usage:** 4 "AA" size (6 Vdc) alkaline batteries (included)  
**Battery Life:** Approximately 40 hours normal use  
**Snake Tube Length:** 39 cm (15")  
**Auto Power OFF:** 10 minutes  
**Warm-Up Time:** Approximately 90 sec  
**Operating Temperature and Humidity:** 0 to 40°C (32 to 104°F), <80% RH



LDH-380, £113.




Comes with 4 "AA" alkaline batteries, complete operator's manual, leak check bottle and carrying case.

**Storage Temperature and Humidity:** -10 to 60°C (14 to 140°F), <70% RH  
**Altitude:** < 2000 m (6500')  
**Dimensions:** 173 x 66 x 56 mm (6.8 x 2.6 x 2.2")  
**Weight:** Approximately 400 g (14 oz)

**MOST POPULAR MODELS HIGHLIGHTED!**

## To Order (Specify Model Number)

Model No.	Price	Description
LDH-380	£113.00	Handheld refrigerant leak detector
MN1500-4	1.60	Package of 4 "AA" replacement batteries
ME-1737	27.00	Reference Book: Liquid Cooling of Electronic Devices 

Comes with 4 "AA" alkaline batteries, complete operator's manual, leak check bottle and carrying case.  
**Ordering Example:** LDH-380, refrigerant leak detector for R-134A, R410A, R-407C, and R22 Freon gas, £113.



## UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

## CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

## GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

## UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

## FRANCE

[www.omega.fr](http://www.omega.fr)  
088-466-342

## CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

## BENELUX

[www.omega.nl](http://www.omega.nl)  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters