



## Steam-Sterilizable 12 mm Electrodes

- ✓ Universal Industrial Electrodes
- ✓ Strong Glass or Ryton® Construction
- ✓ Universal Mounting with Available 316 SS Installation Fittings
- ✓ -5 to 135°C (25 to 275°F) Operating Temperature
- ✓ Porous PTFE Double Junction
- ✓ 3 m (10') Cable Length with BNC Connector
- ✓ -30°C (-22°F) Shipping Temperature

The construction of these electrodes allows them to withstand the high temperature of sterilization and fouling caused by most biological media. These electrodes are rated for 40.5 psi @ 131°C (268°F) and deliver long-term stability despite minimum maintenance.







	pH
Page	D-62
Model	PHE-5432-10
Range	0 to 14 pH
Junction	PTFE double
Length	127 mm (5.0")
Pressure	500 psi @ 25°C (77°F)
Price	\$145

**Note:** Optional PT100 or PT1K ATC (built-in temperature compensation) is available for PHE-5431-10 and PHE-5432-10; add suffix "-PT100" and "-PT1K" to model number and \$40 to price.

25 mm port gland for fermentation vessels.



Thick-Wall Glass	PPS	PAS	PPS
			
<b>ORP</b>	<b>Triple Junction</b>	<b>PAS Body</b>	<b>T Handle pH</b>
D-62	D-59	D-61	D-61
<b>ORE-5432-10</b>	<b>PHE-5433-10</b>	<b>PHE-5431-10</b>	<b>PHE-5431-10-T</b>
±1999 mV	0 to 14 pH	0 to 14 pH	0 to 14 pH
PTFE double	PTFE triple	PTFE double	PTFE double
130 mm (5.1")	135 mm (5.3")	127 mm (5.0")	150 mm (5.90")
500 psi @ 25°C (77°F)	500 psi @ 25°C (77°F)	500 psi @ 25°C (77°F)	150 psi @ 25°C (77°F)
<b>\$185</b>	<b>\$195</b>	<b>\$145</b>	<b>\$165</b>

**PAS:** Polyaryl sulfone.

**PPS:** Polyphenyl sulfide Rytort®.

**Ordering Example:** PHE-5432-10, pH electrode, PHEH-51S installation fitting required for first-time installation. ¼ MNPT, 316 SS, \$145 + 120 = \$265.

## Fittings Selection Guide

**MOST POPULAR MODELS HIGHLIGHTED!**

Model No.	Price	Description
PHEH-51	\$120	½ MNPT, 316 SS
PHEH-51S	120	¼ MNPT, 316 SS
PHEH-52	138	1 MNPT, 316 SS
PHEH-51PG	270	25 mm port gland, 316 SS

## Accessory

Model No.	Price	Description
FW-332	\$79	Reference Book: Advanced pH Measurement and Control





#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters