



pH FIELD & LAB INSTRUMENTS

Benchtop pH Meters Ion Analyzers with RS-232C Interface

PHI-359
\$1260



Electronics Only

- ✓ Direct Concentration Readings
- ✓ Autocalibration for Ion Concentration and pH
- ✓ Recorder Output
- ✓ RS-232C Output

The model PHI-359 benchtop analyzer provides both ion concentration and pH measurements. In the ion measuring mode, the PHI-359 displays measurements in direct concentration values, eliminating the need for evaluating mV values. In the ion concentration calibrating mode, the meter calculates the relationship between two standards and stores this in memory; this avoids the need to manually plot a calibration curve.

Specifications

Measurement Range:

Concentration: 0.001 to 1990

pH: 0 to 14 pH

mV: ±400 mV or ±2000 mV (Autoranges)

Temperature: -30 to 130°C (-22 to 266°F)

Accuracy:

Concentration:

±0.5%

pH: ±0.02 pH

mV: ±0.2% ±1 digit

Temperature: ±0.3°C

Resolution:

Concentration: To 0.001

pH: 0.02

mV: 0.1 mV or 1 mV

Temperature: 0.1°C

Calibration: Automatic or Manual

Automatic Calibration:

Concentration: 2 points

pH: Recognizes buffers 4, 7 and 10

Temperature Compensation: Automatic or Manual, 0 to 99.9°C (32 to 212°F)

Recorder Output: 0 to 200 mV

RS-232C Output: 1200 baud

Manual Mode: Output of pH, ion and temperature values

Automatic Mode: Output of all parameters on demand

Power: 9 V battery or 115 Vac adaptor (included)

Display: 12.7 mm (0.5") LCD

Meter Dimensions: 211 L x 305 W x 104 mm H (8.3 x 12 x 4.1")

Meter Weight: 2.9 kg (6.4 lb)



PHI-359, \$1260, shown smaller than actual size.



PHI-359 supplied with pH and temperature probes.



ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
PHI-359	\$1260	pH/ion meter with accessories

Replacement Accessories

Model No.	Price	Description
PHE-4201	\$51	Clear, epoxy-bodied gel-filled combination pH electrode
PHAT-3016	80	Temperature probe
PHA-3067	110	Flexible third arm stand
FW-332	79	Reference Book: Advanced pH Measurement and Control

Includes epoxy-bodied general purpose pH electrode, temperature probe, ac power adaptor, flexible arm stand and operator's manual.

Ordering Example: PHI-359, benchtop pH/ion meter with accessories with PHE-4201, replacement clear, epoxy-bodied gel-filled combination pH electrode, \$1260 + 51 = \$1311

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters