

TOUCH-SAFE HEATER 50 TO 150 W

NEW

CS060 Series
Starts at
\$48



- Low Surface Temperature
- Quick Mounting Due to Clip Fixing
- Double Insulated (Plastic)
- Wide Voltage Range
- Small Size

Touch-safe heater for the use in enclosures with electrical/electronic components. The design of the heater supports the natural convection which results in a high air-current of warm air. The surface temperatures on the accessible side surfaces of the housing are kept down as a result of the heater design. Our complete range of thermostats and hygrostats can directly be connected to the heater CS060. This heater is also available in a version with plug-in thermostat requiring no additional wiring (CSF060). Both versions are designed for permanent operation.



CS06006000000,
\$48, shown larger
than actual size.

SPECIFICATIONS

Operating Voltage: 120 to 240 Vac/Vdc* (min 110V, max 265V)

Heating Capacity: See table

Heating Element: PTC resistor: temperature limiting

Surface Temperature: <80°C (176°F), except upper protective grille

Connection: 4-pole terminal 2.5 mm² (1.0 in²), torque 0.8 Nm max

Casing: Plastic according to UL94 V-0, black

Mounting: Clip for 35 mm (1.4") DIN rail, EN 50022

Fitting Position: Vertical
Temperature

Operating: -20 to 70°C (-4 to 158°F)

Storage: -45 to 70°C (-49 to 158°F)

Protection Type/Protection Class:

NEMA 2 (IP20)/II (double insulated)

Approvals: VDE + UL File No. E150057 (according to UL499 in combination with UL508A)



Note: Other voltages on request

** Operating with voltages below 140 Vac/Vdc reduces heating performance by approximately 10%.*

Model No.	CS06006000000	CS06006010000	CS06006020000
Heating Capacity¹	50 W	100 W	150 W
Inrush Current Max	2.5 A	4.5 A	8 A
Air Outlet Temperature²	86°C (186.8°F)	120°C (248°F)	145°C (293°F)
Dimensions	110 x 60 x 90 mm (4.3 x 2.4 x 3.5")	110 x 60 x 90 mm (4.3 x 2.4 x 3.5")	150 x 60 x 90 mm (5.9 x 2.4 x 3.5")
Weight (Approx)	0.30 kg (10.6 oz)	0.30 kg (10.6 oz)	0.50 kg (17.6 oz)

¹ Ambient temperature: See heating capacity/ambient temperature diagram

² Measured 50 mm (2") above protective grille



To Order (Specify Model Number)		AVAILABLE FOR FAST DELIVERY!
MODEL NO.	PRICE	DESCRIPTION
CS06006000000	\$48	Enclosure heater, 50 W, 120 to 240 Vac/Vdc
CS06006010000	69	Enclosure heater, 100 W, 120 to 240 Vac/Vdc
CS06006020000	79	Enclosure heater, 150 W, 120 to 240 Vac/Vdc

Comes complete with operator's manual.
Ordering Example: CS06006000000, enclosure heater, \$48.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters