

DUAL ZONE DRUM HEATER

FCDDH-3200-240

\$1299



- ✓ Easy-to-Use Digital Temperature Controller with Audible/Visual Alarm
- ✓ Large Heater Coverage and High Wattages for Fast Heat-Up
- ✓ High Wattage 3200W (1600W Per Zone)
- ✓ 25 mm (1") Fiberglass Insulation
- ✓ Designed for 55 Gallon Metal Drums

OMEGALUX® full-coverage drum heaters are designed to wrap around a drum and heat the contents while insulating to keep the heat exactly where it needs to be. Full-coverage drum heaters combine the convenience of quick heat-up time and the precision of a digital controller to provide the most practical, efficient means of freeze protection, viscosity control, and maintenance of materials at elevated temperatures. The dual zone drum heater provides a fully heated area with independent temperature control for each zone. It is designed to quickly melt heavy solids like molasses, syrups, etc.

FCDDH-3200-240, \$1299, shown smaller than actual size.



SPECIFICATIONS

Digital On/Off Temperature Controller: 10 to 232°C (50 to 450°F) for metal drums

Heated Area: Fully heated

Wattage: 3200W (1600W per zone)

Max Exposure Temperature: 260°C (500°F)

Outer Sheath: Silicone-coated fiberglass facing

Inner Sheath: Silicone-coated fiberglass liner

Insulation: 25.4 mm (1") fiberglass

Dielectric Strength: Over 2000V

Power Cord: 1.8 m (6') with stripped lead ends

Power: 240 Vac (grounded heating element meets NEC 427.23)

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

MODEL NO	PRICE	DESCRIPTION
FCDDH-3200-240	\$1299	Dual zone drum heater
ACCESSORIES		
FCDG-TOP	\$89	Drum top cover
FCDH-STRIP	68	Expander strip for rolling drums with removable lids
PE-1018	220	Reference Book: The Control Handbook

All drum heaters are for 55 gallon size and come with two digital temperature controllers. **Ordering Example:** FCDDH-3200-240, dual zone drum heater for 55 gallon size, 240V, 3200W, with a digital temperature controller for each zone and FCDH-TOP insulation cover that fits on the top of a drum to help prevent heat loss, \$1299 + 89 = **\$1388**.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters