



DRUM HEATERS

FCDH Series
\$1024
 All Models



- ✓ 55 Gallon Wraparound
- ✓ Easy-to-Use Digital Temperature Controller with Audible/Visual Alarm
- ✓ Low Watt Density
- ✓ Silicone-Coated Fiberglass Facing
- ✓ 25 mm (1") Fiberglass Insulation
- ✓ Metal and Poly Drum Models

The FCDH Series consists of full-coverage insulated drum heaters that provide a safe and efficient method of temperature and viscosity control. An easy-to-use digital temperature controller prevents temperature runaway. These heaters use a patented grounded heating element and are designed for indoor use when it is desirable to insulate the entire surface of the drum.

SPECIFICATIONS

Digital On/Off Temperature Controllers:

Metal Drums: 10 to 232°C (50 to 450°F)

Poly Drums: 10 to 71°C (50 to 160°F)

Max Exposure Temperature: 260°C (500°F)

Outer Sheath: Silicone-coated fiberglass facing

Inner Sheath: Silicone-coated fiberglass liner

Insulation: 25.4 mm (1") fiberglass

Dielectric Strength: Over 2000V

Power Cord: 1.8 m (6') with plug on 120V models, stripped lead ends on 240V models

Power: 120 or 240 Vac



FCDH-1600-120, \$1024, shown smaller than actual size.



ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)					
Model No.	Price	Description	Type	Wattage	Voltage
FCDH-1600-120	\$1024	Drum heater	Metal	1600	120
FCDH-750-120	1024	Drum heater	Plastic	750	120
FCDH-1600-240	1024	Drum heater	Metal	1600	240
FCDH-750-240	1024	Drum heater	Plastic	750	240
Accessories					
FCDH-TOP	\$89	Drum top cover			
FCDH-STRIP	68	Expander strip for rolling drums with removable lids			
PE-1405	86	Reference Handbook: The Control of Boilers			

All drum heaters are for 55 gallon size and comes with a digital temperature controller. The 120 Vac models include a 3-prong plug, and the 240 Vac models have stripped leads. **FCDH-TOP** is an insulation cover that fits on the top of a drum to help prevent heat loss. **Ordering Example:** FCDH-1600-120, drum heater for 55 gallon size, 120V, 1600 W, with a digital temperature controller, FCDH-TOP, insulation cover that fits on the top of a drum to help prevent heat loss, \$1024 + 89 = \$1113.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters