

CLEAN WATER 1- OR 3-PHASE IMMERSION HEATER—2½ NPT FITTING

MT-3 Series
Starts at
\$320



MT-330E2/480V/3P, \$550,
shown larger than actual size.




MT-330A/480V/3P, \$320,
shown smaller than actual size.



- ✓ Heavy-Duty Construction
- ✓ Models Available with Explosion-Resistant Enclosure
- ✓ 1.2 cm (0.475") Diameter Copper Sheath, Ideal for 6 to 8 pH Liquids
- ✓ 3 to 18 kW
- ✓ 120, 208, 240, and 480 Vac; 1- and 3-Phase Power

Note: This immersion heater should be used with an approved temperature control device to ensure safe operation. See Section P for our selection of process controllers. Not intended for use in hazardous areas. (See previous pages for caution and warnings.)



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

kW	Volts	W/in ²	No. Htg. Elemt.	Dim. B cm (in)	E1 General Purpose Enclosure ¹			E2 Explosion/Moisture-Res. Encl. ²		
					Model No.	Price	Wt. kg (lb)	Model No.	Price	Wt. kg (lb)
3	240	51	3	19 (7%)	MT-330A/** [†]	\$320	3 (5)	MT-330E2/*	\$550	4 (8)
3.75	240	52	3	21 (8%)	MT-337A/** [†]	350	3 (6)	MT-337E2/*	600	4 (9)
4.5	120	48	3	30 (11%)	MT-345A/** [†]	390	3 (6)	MT-345E2/*	625	4 (9)
6	120	48	3	44 (17%)	MT-360A/** [†]	455	4 (8)	MT-360E2/*	700	4 (9)
7.5	208	53	3	49 (19%)	MT-375A/** [†]	500	4 (8)	MT-375E2/*	750	4 (9)
9	208	47	3	62 (24%)	MT-390A/** [†]	600	6 (12)	MT-390E2/*	825	7 (15)
12	208	46	3	82 (32%)	MT-3120A/** [†] ³	725	6 (13)	MT-3120E2/* ³	975	6 (16)
15	208	46	3	101 (39%)	MT-3150A/** [†] ³	875	7 (14)	MT-3150E2/* ³	1100	8 (17)
18	208	46	3	120 (47%)	MT-3180A/** [†] ³	1000	7 (15)	MT-3180E2/3P ³	1250	8 (18)

^{*} Designate voltage: insert "120V" for 120 Vac, "208V" for 208 Vac, "240V" for 240 Vac or "480V" for 480 Vac.

^{**} Designate voltage: insert "208V" for 208 Vac, "240V" for 240 Vac or "480V" for 480 Vac.

[†] Insert the suffix "3P" after model number for 3-phase power.

¹ Heaters with general purpose enclosures are UL listed and CSA certified.

² Heaters with moisture-resistant/explosion-resistant enclosures are CSA NRTL/C certified.

³ Not UL listed, CSA certified or CSA NRTL/C certified (exceeds 48 amps).

Ordering Examples: MT-330A/240V/3P, 3 kW heater powered by 3-phase 240V, \$320.

MT-337E2/120V/3P, 3 kW heater powered by 3-phase 120V, \$600.



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters