

RUGGED PROCESS WATER IMMERSION HEATER WITH 2½ NPT FITTING

MTS-3 Series

Starts at

\$568



NRTL/C

- ✓ Stainless Steel Wetted Construction
- ✓ 120, 208, 240, 480 V;
1- and 3-Phase Power
- ✓ Reliable Heater Design
- ✓ General Purpose Enclosure, NEMA 1 (IP00) Rated and UL Listed

Please Note: This immersion heater should be used with an approved temperature control device to ensure safe operation. See Section P for our selection of process controllers.



See Previous Pages for Caution and Warnings!



MTS-330E2/480V/3P, \$795, shown smaller than actual size.



MTS-360A/480V/3P, \$752, shown smaller than actual size.



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)									
kW	W/in ²	No. Htg. Elem.	Dim. B cm (in)	E1 Gen. Purpose Enclosure ¹			E2 Moist-/Explos-Res. Enc. ²		
				Model No.	Price	Wt. kg (lb)	Model No.	Price	Wt. lb (kg)
3	51	3	17 (6⅞)	MTS-330A/**/***	\$568	2 (5)	MTS-330E2/**/***	\$795	4 (8)
4.5	48	3	28 (10⅞)	MTS-345A/**/***	652	3 (6)	MTS-345E2/**/***	845	4 (9)
6	48	3	43 (16⅞)	MTS-360A/**/***	752	3 (6)	MTS-360E2/**/***	942	4 (9)
7.5	53	3	49 (18⅞)	MTS-375A/**/***	828	3 (6)	MTS-375E2/**/***	1048	4 (9)
9	47	3	61 (24)	MTS-390A/208V/**/***	931	3 (7)	MTS-390E2/**/***	1152	5 (10)
12	46	3	81 (31⅞)	†MTS-3120A/208V/**/***	1119	4 (9)	†MTS-3120E2/**/***	1316	5 (12)
15	46	3	101 (39⅞)	†MTS-3150A/208V/**/***	1360	5 (10)	†MTS-3150E2/**/***	1553	6 (13)
18	51	3	118 (46⅞)	†MTS-3180A/208V/**/***	1497	5 (12)	†MTS-3180E2/**/***	1733	7 (15)

*Designate voltage: insert "120" for 120 Vac, "208" for 208 Vac, "240" for 240 Vac or "480" for 480 Vac.

** Designate voltage: insert "208" for 208 Vac, "240" for 240 Vac or "480" for 480 Vac.

*** Add suffix "3P" to the model number for 3-phase power, no extra charge (not available for 120 V models).

¹ Heaters with general purpose enclosures are UL listed and CSA certified except models with † (exceed 48 amps).

² Heaters with moisture-resistant/explosion-resistant enclosures are CSA NRTL/C certified and are not intended for use in hazardous areas, except models with † (exceed 48 amps).

Ordering Example: MTS-330A/480V, 3 kW heater powered by 1-phase 480 Vac, \$568.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters