



SCREW PLUG IMMERSION HEATERS CLEAN WATER APPLICATIONS

MT Series
Starts at
\$119



- ✓ 1 NPT Brass Screw Plug
- ✓ Copper Sheath Element
- ✓ High Watt Density (64 to 86 W/in²)
- ✓ 0.75 to 3 kW
- ✓ Without Thermostat
- ✓ 120 and 240V, 1 Phase
- ✓ General Purpose or Moisture-Resistant/Explosion-Resistant Terminal Enclosure

Note: This immersion heater should be used with an approved temperature control device to assure safe operation.

SPECIFICATIONS


Wattage: 0.75 to 3 kW

Power: 120 or 240V, 1 phase

Watt Density: 64 to 86 W/in²


Screw Plug: 1 NPT brass screw plug

Enclosures: E1 general purpose, NEMA 1 rated, or type E2 moisture-resistant/explosion-resistant enclosure.²



MT-1000/120,
\$126, shown
smaller than
actual size.

MT-1000E2/120,
\$339, shown
smaller than
actual size.



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)											
kW	Volts	W/in ²	No. Htg. Elem.	E1 General Purpose Enclosure ¹				E2 Moisture Resis/Explosion Resis. ²			
				Dim. B cm (in)	Model No.	Price	Wt. kg (lb)	Model No.	Price	Wt. kg (lb)	
0.75	120	64	1	16 (6 ⁵ / ₁₆)	MT-750/*	\$119	0.9 (2)	MT-750E2/*	\$332	2.3 (5)	
0.75	240	64	1	16 (6 ⁵ / ₁₆)	MT-750/*	119	0.9 (2)	MT-750E2/*	332	2.3 (5)	
1	120	85	1	16 (6 ⁵ / ₁₆)	MT-1000/*	126	0.9 (2)	MT-1000E2/*	339	2.3 (5)	
1	240	85	1	16 (6 ⁵ / ₁₆)	MT-1000/*	126	0.9 (2)	MT-1000E2/*	339	2.3 (5)	
1.25	120	83	1	20 (8 ¹ / ₁₆)	MT-1250/*	135	0.9 (2)	MT-1250E2/*	347	2.3 (5)	
1.25	240	83	1	20 (8 ¹ / ₁₆)	MT-1250/*	135	0.9 (2)	MT-1250E2/*	347	2.3 (5)	
1.5	120	86	1	23.5 (9 ³ / ₄)	MT-1500/*	143	0.9 (2)	MT-1500E2/*	355	2.3 (5)	
1.5	240	86	1	23.5 (9 ³ / ₄)	MT-1500/*	143	0.9 (2)	MT-1500E2/*	355	2.3 (5)	
2	120	83	1	31 (12 ¹ / ₄)	MT-2000/*	161	0.9 (2)	MT-2000E2/*	373	2.3 (5)	
2	240	83	1	31 (12 ¹ / ₄)	MT-2000/*	161	0.9 (2)	MT-2000E2/*	373	2.3 (5)	
2.5	120	79	1	41 (16 ¹ / ₄)	MT-2500/*	178	0.9 (2)	MT-2500E2/*	391	2.3 (5)	
2.5	240	79	1	41 (16 ¹ / ₄)	MT-2500/*	178	0.9 (2)	MT-2500E2/*	391	2.3 (5)	
3	120	78	1	50 (19 ⁵ / ₁₆)	MT-3000/*	196	1.4 (3)	MT-3000E2/*	408	2.7 (6)	
3	240	78	1	50 (19 ⁵ / ₁₆)	MT-3000/*	196	1.4 (3)	MT-3000E2/*	408	2.7 (6)	

* Designate voltage, i.e., "120" for 120 Vac or "240" for 240 Vac.

¹ Heaters with general purpose enclosures are UL Listed and CSA certified.

² Heaters with moisture-resistant/explosion-resistant enclosures are CSA NRTL/C certified and are not intended for use in hazardous areas.

Ordering Example: MT-750/240, 0.75 kW heater powered by 240 Vac, \$119.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters