

SILICONE RUBBER LAMINATED DRUM HEATERS

SHDH Series
Starts at

\$157

Heavy Duty Drum Heaters

- ✓ Low Watt Density Electrical Resistance Heater
- ✓ 4.5 Watts/Sq. Inch Exposure Temperature up to 232°C (450°F)
- ✓ Rugged and Flexible Heater Element
- ✓ Constant Watt Density
- ✓ Quick and Simple Installation
- ✓ Moisture and Chemical Resistant
- ✓ Economical
- ✓ Dense Grounding Grid of Tinned Copper Wire

OMEGALUX® silicone rubber laminated heavy duty drum Heaters are electrical resistance heaters in blanket form. They are designed to provide a practical efficient means of freeze protection, viscosity control, melting of solids and maintaining materials at elevated temperatures.

OMEGALUX heavy duty drum heaters are totally integrated heating systems consisting of a durable, multi-strand nickel-chromium heating element insulated with two applications of high temperature fiberglass yarn and knitted into tape form. These tapes are laminated between multiple layers of silicone impregnated fiberglass cloth and a



dense grounding grid of tinned copper wire. This thin line design enables use of the standard drum and cradle without any modifications to either. It is thin enough to fit between the drum and its cradle, a problem commonly encountered with other drum heaters.

The optional OMEGALUX thermostatic control combined with the low watt density serpentine heating element ensures even heat distribution across the entire inner surface of the drum

heater and provides a positive prevention from hot spots and overheating sensitive products.

SPECIFICATIONS

Power: 120 and 240V
Wattage: 600, 698, 965, 1200 W
Maximum Continuous Exposure Temperature: 232°C (450°F)
Thickness: 1/8"
Width: 4"
Closure: one heavy duty spring
Dielectric Strength: 2000V
Watts/Square Inch: 4.5

SHDH Series

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

55 gal, 1200 W, 66.5" long			30 gal 1000 W, 54" long			15 gal, 698 W, 40" long			5 gal, 550 W, 31" long		
Models Without Adjustable Thermostat*											
Volts	Model No.	Price	Volts	Model No.	Price	Volts	Model No.	Price	Volts	Model No.	Price
120	SHDH-1200-120	\$197	120	SHDH-1000-120	\$183	120	SHDH-698-120	\$157	120	SHDH-550-120	\$138
240	SHDH-1200-240	197	240	SHDH-1000-240	183	240	SHDH-698-240	157	240	SHDH-550-240	138
Models With Adjustable Thermostat 50° to 425°F									5 gal, 600 W, 31" long		
Volts	Model No.	Price	Volts	Model No.	Price	Volts	Model No.	Price	Volts	Model No.	Price
120	SHDH-C-1200-120	\$254	120	SHDH-C-1000-120	\$220	120	SHDH-C-698-120	\$206	120	SHDH-C-600-120	\$186
240	SHDH-C-1200-240	254	240	SHDH-C-1000-240	220	240	SHDH-C-698-240	206	240	SHDH-C-600-240	186

Heaters are supplied with 6¹/₈" HSJO 3 prong plug. Plugs are not provided on 240V drum heaters.

* Remote temperature control recommended. See CPP and CBC Series temperature controllers on the web.

Ordering Example: SHDH-1200-240, 240V drum heater for a 55 gallon drum, \$197.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters