

IMMERSION HEATERS FOR SMALL TANK APPLICATIONS

Basic Unit
\$124


Style TMW-2

- ✓ 1 1/4" NPT Brass Screw Plug
- ✓ Copper Sheath Element
- ✓ 64 - 86 W/In²
- ✓ 750 - 5,000 Watts
- ✓ 120 and 240 Volt, Single Phase
- ✓ Without Terminal Cover
- ✓ Without Thermowell


APPLICATION

- Clean Water Heating

Dimensions (Inches)



Dimensions (Inches)



To Order (Specify Model Number)

Watts	Volts	Phase	W/In ²	DIM B (In.)	Model No.	Price	Wt. (Lb.)
Straight Element							
750	120	1	64	6-1/8	TMW-207A/120	\$124	0.5
750	240	1	64	6-1/8	TMW-207A/240	124	0.5
1,000	120	1	85	6-1/8	TMW-210A/120	136	0.5
1,000	240	1	85	6-1/8	TMW-210A/240	136	0.5
1,250	120	1	82	7-7/8	TMW-212A/120	150	1
1,250	240	1	82	7-7/8	TMW-212A/240	150	1
1,500	120	1	86	9-1/16	TMW-215A/120	161	1.25
1,500	240	1	86	9-1/16	TMW-215A/240	161	1.25
Foldback Element							
2,000	120	1	85	6-5/8	TMW-220A/120	188	1.5
2,000	240	1	85	6-5/8	TMW-220A/240	188	1.5
2,500	240	1	80	8-1/2	TMW-225A/240	209	2
3,000	240	1	78	10-3/16	TMW-230A/240	242	2.25
4,000	240	1	77	13-9/16	TMW-240A/240	268	2.5
5,000	240	1	76	16-15/16	TMW-250A/240	288	3

Ordering Example: TMW-212A/120, is a 120 V, Single Phase, 1,250 Watt Heater, \$150.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters