

1/8 DIN RATEMETERS, TOTALIZERS, AND BATCH CONTROLLERS For Frequency Inputs

DPF76
Starts at
\$238



- ✓ Front-Panel Programming and Scaling
- ✓ Rate and Total in One Unit
- ✓ Remote or Front-Panel Reset
- ✓ Optional Analog Output for Rate or Total
- ✓ NEMA 4X (IP66) Front Panel

The DPF75 is a combination 6-digit totalizer/batch controller and 5½ digit ratemeter with 2 relays. The user can set one relay for batch and the other for rate alarm. The totalizer and ratemeter display in the same engineering units: units per second, minute, or hour. The DPF75 can accept 2 inputs and separately scale them for "A - B" or "A + B". Either input A rate or net total can be displayed.

The DPF76 is a 6-digit scalable totalizer/batch controller with 2 relays for 2-stage batch control. The DPF78 is a 4½ digit scalable ratemeter with 2 alarm relays.

SPECIFICATIONS

Input Power: 110 Vac ±15%, 220 Vac ±15%, 6.5 VA at rated AC voltage

Output Power (AC-Powered Units Only): +12 Vdc @ 50 mA unregulated—10 + 50%

Rate Accuracy: ±0.1% of rdg + 1 LSD

K Factor: Up to 5-digits

Temperature:

Operating: 0 to 54°C (32 to 129°F)

Storage: -40 to 93°C (-40 to 199°F)

Memory: EEPROM stores data for 10 years if power lost

Pulse Input: Low = 0 to 1 Vdc; high = 4 to 30 Vdc; 10 kΩ impedance, up to 10 kHz; min 0.05 Hz for rate indication



DPF75 1/8 DIN, \$278, shown actual size.

Option "-LL": 30 mV min to 50V max p-p input, 10 kΩ impedance, 5 kHz max

Relays: Rated 5 A @ 240 Vac or 28 Vdc; SPST, selectable for NO or NC; relays latch or auto-recycle after 0.1 to 99.9 s

Panel Cutout: 4.5 H x 9.2 cm W (1.772 x 3.622"); DIN standard, 10.3 cm (4.06") depth

Shipping Weight: 907 g (2 lb)



OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
DPF75	\$278	Ratemeter and batch controller with 2 separate 5 A SPST relays for rate alarm or batching
DPF76	238	Scalable totalizer/batch controller with relays
DPF78	255	Scalable ratemeter with 2 separate 5 A SPST alarms

Options

Ordering Suffix	Add'l Cost	Description
-A	\$131	Analog output, 0 or 4 to 20 mA proportional to rate/total*
-LL	59	Low level magnetic input A, 30 mV range
-220	N/C	220 Vac power
-RS232	131	RS232 communications*
-RS422	131	RS422 communications*

* "-A", "RS232" and "RS422" options are mutually exclusive. Only one may be ordered with a unit.

Accessories

Model No.	Price	Description
DPP-5	\$525	1/8 DIN panel punch
FLSC-AMP	70	Amplifier for low-level turbine and paddlewheel sensor inputs

Comes complete with operator's manual.

Ordering Examples: DPF75-RS232-LL, ratemeter/batch controller with RS232 output, and low-level input option, \$278 + 131 + 59 = \$468.

DPF75, totalizer/batch controller, OCW-3, OMEGACARESM extends standard 2-year warranty to a total of 5 years (\$70), \$278 + 70 = \$348.

Recommended Reference Book: Instrumentation & Control Systems, FW-317, \$63. See Section Y for Additional Books



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters