


OPTIONS AND ACCESSORIES

LOAD BUTTONS AND ROD ENDS

FOR IMPERIAL LOAD CELLS




Dimensions: mm (in)

Load Buttons (Specify Model Number)

MODEL	PRICE	THREAD	H	T	D	F	R
LBC-014	\$40	1/4-28	13 (0.50)	5 (0.20)	15 (0.60)	13 (0.50)	51 (2.0)
LBC-038	40	3/8-24	15 (0.60)	8 (0.30)	19 (0.75)	16 (0.63)	51 (2.0)
LBC-012	40	1/2-20	18 (0.70)	8 (0.30)	19 (0.75)	16 (0.63)	102 (4.0)
LBC-034	55	3/4-16	23 (0.90)	8 (0.30)	38 (1.50)	32 (1.25)	152 (6.0)
LBC-100	55	1-14	28 (1.10)	8 (0.30)	38 (1.50)	32 (1.25)	203 (8.0)
LBC-101	55	1-12	28 (1.10)	8 (0.30)	38 (1.50)	32 (1.25)	203 (8.0)
LBC-114	60	1 1/4-12	38 (1.50)	13 (0.50)	51 (2.00)	44 (1.75)	254 (10.0)
LBC-112	70	1 1/2-12	57 (2.25)	25 (1.00)	64 (2.50)	57 (2.25)	356 (14.0)
LBC-200-12	*	2-12	89 (3.50)	28 (1.10)	57 (2.25)	44 (1.75)	203 (8.0)
LBC-300-8	*	3-8	133 (5.25)	47 (1.86)	83 (3.25)	67 (2.63)	305 (12.0)

* Consult Engineering.

Load Button Dimensions



Load Cell Options (Limited Models Only)

Temperature Compensation:

"-TC1" extended compensated range
(-46 to 93°C/-50 to 200°F) not
exceeding operating range.....

\$50

"-TC2" 163°C (350°F).....

225

Additional Cable Length:

4-conductor PVC.....

\$2.00/ft

4-conductor PTFE.....

4.50/ft

6-conductor PVC.....

2.75/ft

6-conductor PTFE.....

6.50/ft

Mating Connectors:

PT06F-10-6S.....

\$26.50

PT06A-10-6S (SR).....

25.00

Calibration/Recalibration:

"-NC5" 5-point calibration.....

\$150.00



0%, 50%, 100%, 50%, 0%

Extra calibration points.....

\$25/pt

See Page B-12 for full details on calibrations

Rod End Dimensions



Built-In Amplifiers:

0 to 5 Vdc.....

\$175

4 to 20 mA.....

195

In-Line Amplifiers:

See section C for selection

Rod Ends (Specify Model Number) Dimensions: mm (in)

MALE ROD ENDS	PRICE	THREAD UNF-3A	B	W	H	A	D	C	a°	K	J	STATIC LOAD (lb)	WT. (lb)
REC-010M*	\$10	10-32	5 (0.190)	8 (0.312)	6 (0.234)	32 (1.25)	16 (0.625)	19 (0.750)	17	—	—	1170	0.03
REC-014M	25	1/4-28	5 (0.190)	8 (0.312)	6 (0.250)	40 (1.562)	19 (0.750)	25 (1.000)	10	—	—	2158	0.04
REC-038M	25	3/8-24	8 (0.3125)	11 (0.437)	9 (0.344)	49 (1.938)	25 (1.000)	32 (1.250)	12	—	—	5323	0.25
REC-012M	45	1/2-20	11 (0.4375)	14 (0.562)	11 (0.437)	62 (2.438)	33 (1.312)	38 (1.500)	12	—	—	23,452	0.25
REC-058M	69	5/8-18	13 (0.5000)	16 (0.625)	13 (0.500)	67 (2.625)	38 (1.500)	41 (1.625)	10	—	—	31,390	0.38
REC-034M	65	3/4-16	16 (0.6250)	19 (0.750)	14 (0.562)	73 (2.875)	44 (1.750)	44 (1.750)	13	—	—	40,572	0.60
REC-100M	135	1-14	25 (1.000)	35 (1.375)	25 (1.000)	105 (4.125)	70 (2.750)	545 (2.120)	14	—	—	43,541	2.1
REC-114M	150	1 1/4-12	32 (1.250)	28 (1.093)	24 (0.937)	105 (4.125)	70 (2.750)	54 (2.125)	7	—	—	44,500	2.4
REC-112M	185	1 1/2-12	38 (1.500)	33 (1.312)	29 (1.125)	137 (5.375)	89 (3.500)	76 (3.000)	6.5	—	—	138,826	4.8
FEMALE ROD ENDS	PRICE	UNF-2B	B	W	H	A	D	C	a°	K	J	STATIC LOAD (lb)	WT. (lb)
REC-006F*	\$10	6-32†	3 (0.1250)	6 (0.250)	5 (0.187)	21 (0.812)	13 (0.500)	11 (0.437)	16	8 (0.312)	6 (0.250)	1202	0.02
REC-010F*	10	10-32	5 (0.190)	8 (0.312)	6 (0.234)	27 (1.062)	16 (0.625)	13 (0.500)	17	10 (0.406)	8 (0.312)	2028	0.04
REC-012F	35	1/2-20	13 (0.500)	16 (0.625)	13 (0.500)	54 (2.125)	33 (1.312)	30 (1.187)	12	22 (0.875)	19 (0.750)	16,238	—
REC-014F	10	1/4-28	6 (0.250)	10 (0.375)	7 (0.265)	33 (1.312)	19 (0.750)	17 (0.687)	21	12 (0.469)	10 (0.375)	3114	0.05
REC-034F	65	3/4-16	19 (0.750)	22 (0.875)	17 (0.687)	73 (2.875)	44 (1.750)	44 (1.750)	14	29 (1.125)	25 (1.000)	28,081	—
REC-038F	25	3/8-24	10 (0.375)	13 (0.500)	10 (0.406)	41 (1.625)	25 (1.000)	24 (0.937)	12	17 (0.687)	14 (0.562)	9544	—

* Not available with grease fitting.

† UNC thread.

omega.co.uk®

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters