

# LOW-PRESSURE DIAPHRAGM GAUGES

## PGL Series


All Models  
**\$40**



- ✓ Corrosion-Resistant Bronze Diaphragm
- ✓ 150% Overpressure Protection
- ✓ Recalibration Screw on Dial
- ✓ 2-1-2 ANSI Grade A Accuracy\*

### SPECIFICATIONS

Dial: 64 mm (2.5") Dia.  
 Pointer: Black aluminum  
 Movement: Brass  
 Element: Bronze diaphragm  
 Connection: 1/4 NPT  
 Window: Polycarbonate  
 Media: Clean, dry, non-corrosive gas only



PGL-25L-60, \$40, shown larger than actual size.



**MOST POPULAR MODELS HIGHLIGHTED!**

| To Order (Specify Model Number) |             |                          |                         |               |             |             |     |
|---------------------------------|-------------|--------------------------|-------------------------|---------------|-------------|-------------|-----|
| MODEL NO.                       | PRICE       | RANGE/GRADUATIONS        |                         |               |             |             |     |
|                                 |             | OUTER SCALE              | INNER SCALE             | INNER SCALE   |             | OUTER SCALE |     |
| FIG. INTERVALS                  | MINOR GRAD. |                          |                         | FIG INTERVALS | MINOR GRAD. |             |     |
| PGL-25L-10                      | \$40        | 0/10 inH <sub>2</sub> O  | —                       | 1             | 0.1         | —           | —   |
| PGL-25L-15                      | 40          | 0/15 inH <sub>2</sub> O  | 0/9 oz/in <sup>2</sup>  | 1             | 0.2         | 5           | 0.2 |
| PGL-25L-35                      | 40          | 0/35 inH <sub>2</sub> O  | 0/20 oz/in <sup>2</sup> | 5             | 0.5         | 5           | 0.5 |
| PGL-25L-60                      | 40          | 0/60 inH <sub>2</sub> O  | 0/35 oz/in <sup>2</sup> | 5             | 0.5         | 5           | 0.5 |
| PGL-25L-100                     | 40          | 0/100 inH <sub>2</sub> O | 0/60 oz/in <sup>2</sup> | 10            | 1           | 10          | 1   |
| PGL-25L-160                     | 40          | 0/160 inH <sub>2</sub> O | —                       | 20            | 2           | —           | —   |
| PGL-25L-200                     | 40          | 0/200 inH <sub>2</sub> O | —                       | 20            | 2           | —           | —   |
| PGL-25L-300                     | 40          | 0/300 inH <sub>2</sub> O | —                       | 50            | 5           | —           | —   |

\* 2% first 10%, 1% middle 80%, 2% last 10%.

Note: Cannot be oxygen cleaned.

Ordering Example: PGL-25L-100, low-pressure gauge with 0 to 100 inH<sub>2</sub>O range, \$40.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters