

# Thermocouple Assembly Kit

- ✓ Build Micro-Miniature, Standard or Heavy-Duty Thermocouples
- ✓ Provides Cryogenic Through High Temperature Service
- ✓ Create Assemblies in Minutes
- ✓ Contains 4 Thermocouple Types
- ✓ Carrying Storage Case Included

N-965  
**\$445**  
Complete Kit  
with Instructions



Note: The contents of this kit can be purchased separately if desired. If purchased separately, the contents would cost over \$700.

## NOW AVAILABLE

At no extra charge, the OMEGA N-965 can be supplied in 1 or 2 thermocouple combinations instead of an assortment. Specify which combinations you desire.

## Contents

- 12 Color-coded connectors (male and female)—  
3 each: CHROMEGA®-ALOMEGA®, Iron-Constantan, Copper-Constantan and CHROMEGA®-Constantan
- 12 Tube clamps—  
3 each:  $\frac{1}{16}$ ,  $\frac{1}{8}$ ,  $\frac{3}{16}$  and  $\frac{1}{4}$ " sizes
- 12 Cable clamps
- 12 Compression fittings—  
3 each:  $\frac{1}{16}$ ,  $\frac{1}{8}$ ,  $\frac{3}{16}$  and  $\frac{1}{4}$ " sizes
- 8 Inconel, closed-end tubes—6" length  
2 each:  $\frac{1}{16}$ ,  $\frac{1}{8}$ ,  $\frac{3}{16}$  and  $\frac{1}{4}$ " OD
- 8 Stainless steel closed-end tubes—6" length  
2 each:  $\frac{1}{16}$ ,  $\frac{1}{8}$ ,  $\frac{3}{16}$  and  $\frac{1}{4}$ " OD
- 4 Inconel open-end tubes—6" length  
1 each:  $\frac{1}{16}$ ,  $\frac{1}{8}$ ,  $\frac{3}{16}$  and  $\frac{1}{4}$ " OD
- 4 Stainless steel open-end tubes—6" length  
1 each:  $\frac{1}{16}$ ,  $\frac{1}{8}$ ,  $\frac{3}{16}$  and  $\frac{1}{4}$ " OD
- 24 Two-hole insulating tubes—6" length  
6 each:  $\frac{3}{16}$ ,  $\frac{1}{16}$ ,  $\frac{1}{8}$  and  $\frac{3}{16}$ " OD
- 2 Containers CC cement (1 oz)

## AVAILABLE FOR FAST DELIVERY!

- 60 Thermocouples—12" leads  
5 each CHROMEGA®-ALOMEGA® 0.005"  
5 each CHROMEGA®-ALOMEGA® 0.015"  
5 each CHROMEGA®-ALOMEGA® 0.032"  
5 each Iron-Constantan 0.005"  
5 each Iron-Constantan 0.015"  
5 each Iron-Constantan 0.032"  
5 each Copper-Constantan 0.005"  
5 each Copper-Constantan 0.015"  
5 each Copper-Constantan 0.032"  
5 each CHROMEGA®-Constantan 0.005"  
5 each CHROMEGA®-Constantan 0.015"  
5 each CHROMEGA®-Constantan 0.032"  
7.6 m (25') CHROMEGA®-ALOMEGA® 20 AWG extension wire  
7.6 m (25') CHROMEGA®-Constantan 20 AWG extension wire  
7.6 m (25') Copper-Constantan 20 AWG extension wire  
7.6 m (25') Iron-Constantan 20 AWG extension wire

**UNITED STATES**

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

**CANADA**

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

**GERMANY**

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

**UNITED KINGDOM**

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

**FRANCE**

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

**CZECH REPUBLIC**

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

**BENELUX**

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44

**More than 100,000 Products Available!****• Temperature**

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

**• Flow and Level**

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

**• pH and Conductivity**

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

**• Data Acquisition**

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

**• Pressure, Strain and Force**

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

**• Heaters**

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters