



Shown smaller
than actual size

Omni-Amp™ IIA

D.C. Millivolt Amplifier

Battery-Operated Laboratory Model

\$195

- ✓ Heavy-duty case
- ✓ Batteries will last over 500 hours in continuous service.
- ✓ 1.5 V Type C (4 per unit, Model Number - MN1400-4) (Spare set of batteries \$4)
- ✓ Specifications and performance characteristics the same as Model OMNI-AMP I

To Order, Specify:
OMNI-AMP IIA

Omni-Amp™ IIB

Thermocouple D.C. Millivolt Amplifier

Battery-Operated Laboratory with Built-in ice point™ Reference Junction for Cold Junction Compensation

\$285

- ✓ Heavy Duty Case
- ✓ Batteries will last over 500 hours in continuous service.
- ✓ 1.5 V Type C (4 per unit, Model Number - MN1400-4) (Spare set of batteries \$4)
- ✓ RM12R-B 3.6 V "AA" Lithium or equivalent (Spare battery \$8.25 ea.)
- ✓ Other specifications and performance characteristics the same as Model OMNI-AMP I
- ✓ Select any calibration K, J, T, E, S, R, C or D
- ✓ Accepts OST type male connectors

To Order, Specify:
OMNI-AMP IIB-(*)
and Select Thermocouple
Type J, K, T, E, RS, C or D.



Shown smaller
than actual size



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenpfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers, Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters