

IR Electrical Scanner with Autozero Function



OS93
\$699



- ✓ Fast 0.05 s Indications of Temperature Differences
- ✓ Autozero Function
- ✓ Compares Sample Temperatures to Reference Surface Temperature
- ✓ Shirt-Pocket Size
- ✓ Unique Color-Coded LED Bar Graph Indicates Quality Control
- ✓ High-Impact Housing with Copper EMI Shield

Applications

- ✓ Checking Repair Work
- ✓ Preventive Maintenance
- ✓ Scanning at a Distance
- ✓ Monitoring Electrical Connections, Including Transformers, Circuit Breakers, Motors, Cables, Bus Bars, and Power Panels

The OS93 electrical scanner is a patented infrared temperature scanner with autozero function. It is the instrument of choice for professionals who regularly conduct scans of electrical equipment at distances of up to 5'. Insurance and utility companies have issued guidelines for infrared inspection, which has proved a fast, easy, and effective way to locate electrical problems.

The unique scanning display, combined with high-resolution optics, enables the user to locate hot spots clearly and from a safe, convenient distance. The autozero feature locks in the reference



OS93, \$699, shown actual size.



OS93 rear view, \$699, shown smaller than actual size.

temperature, allowing differential measurements. Just push the button, aim at ambient or reference temperature, and scan. The color-coded bar graph indicates the components that need service. The NIST-traceable calibration lasts for the lifetime of the instrument.

Specifications

Autozero Ambient Reference Range:
0 to 50°C (32 to 122°F)

Temperature Range:
0 to >100°C rise above reference

Accuracy: ±1 segment in each range

Resolution: 1°C

Spectral Response: 2 to 20 microns

Spot Size: 0.625" +
(distance in inches/87)

Time Constant: 0.05 s

Emissivity: 0.9 fixed

Power: 9 V battery (included)

Battery Life: 200 min, continuous

Dimensions:

89 H x 127 W x 19 mm D

(3.5 x 5 x 0.75")

Weight: 198 g (7 oz) with battery

OMEGACARESM extended warranty program is available for models shown on this page. Ask your sales representative for full details when placing an order. OMEGACARESM covers parts, labor and equivalent loaners.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Model No.	Price	Description
OS93	\$699	Electrical scanner with autozero function
EE-2451	160	Reference Book: Electronics Handbook

Comes with carrying pouch, 9 V battery, display sun shade and complete operator's manual.

Ordering Example: OS93, electrical scanner, \$699. OCW-2, OMEGACARESM extends standard 2-year warranty to a total of 4 years (\$125), \$699 + 125 = \$824.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters