

Waterproof, Flexible Moulded RTD Surface Temperature Sensors

- ✓ Moisture Protection to IP67 Standard
- ✓ Temperature Range: -30 to 150°C
- ✓ Precision 100 Ω , Class "A" DIN Platinum Element

- ✓ Stripped Leads Standard, Connector Options Available
- ✓ Sensors Have Adhesive Back for Easy Mounting

Starts at £32

Custom Cable Lengths and Pad Shapes Available

1 hour after application to a clean, dry surface the sensors and adhesive will resist moisture to IP67.

50mm

15 mm

7/0.16 mm stranded nickel-plated copper, Silicon insulated cable, 1 m long standard

NEW

SA2C-RTD-3-100-A-1M-IP67, £32, shown smaller than actual size.

IP67

To Order (Specify Model Number)

Model Number	Resistance	Number of Wires	Wire Length	Price
SA2C-RTD-3-100-A-1M-IP67	100 Ω , Class "A" DIN Platinum	4	1 m	£32
SA2C-RTD-3-100-A-2M-IP67	100 Ω , Class "A" DIN Platinum	4	2 m	34
SA2C-RTD-3-100-A-3M-IP67	100 Ω , Class "A" DIN Platinum	4	3 m	36
SA2C-CT-RTD	Pack of 5 self-adhesive cable ties			4.50

Options: For longer cable lengths, change "3M" in model number to length needed and add £2 per metre to the price. For 4-PIN mini DIN connector add "MDIN4" to model number and add £8 to price.

Ordering Example: SA2C-RTD-3-100-A-2M-IP67-MDIN4, 4-wire 100 Ω , Class "A" element, 2M of lead wire & 4-pin mini DIN plug, £42.

SA2C-RTD-3-100-A-1M-IP67, £32, shown smaller than actual size.

SA2C-CT-RTD, self-adhesive cable ties, £4.50/pack of 5.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters