

# Probe Handles with Retractable Cable

**Thermocouple Probes with Built-In USB Coming Soon!**

**0.5 m (1') of Retractable Cable Stretches to 1.5 m (5')!**



SDX-UST universal connector, accepts both standard and miniature connectors.

**PATENTED**  
Covered by U.S. and International patents and pending applications.

SDX **\$25** High-Impact Plastic  
HDX **\$37<sup>50</sup>** Cast Aluminum



Safety clips also available separately, order SFCL, \$0.50/pkg of 10.

SDX-UST connector with handle, \$25

OST standard size connectors.

OMEGA's high-impact (ABS) plastic handles (SDX) and heavy-duty aluminum brobe handles (HDX) provide a fast, easily connected system of handheld probes for a broad range of applications. Sensing elements can be quickly changed or replaced in the field without tools. In addition, the strain relieved retractable can also be replaced by other types of thermocouple wire.

SMP miniature connector.

- ✓ SDX Handles Now Accept Probes with Both Standard and Miniature Connectors!
- ✓ HDX Handles Designed for 2- or 3-Prong Connectors

- ✓ Works Well with Handheld Thermometers
- ✓ Easy Grip Design
- ✓ Allow Quick Change or Replacement
- ✓ High-Impact Plastic or Cast Aluminum Handle Designs



## HDX Aluminum Handles

To Order (Specify Model Number)			
Model Number	Price	Connector in Handle	Connector on Cable
HDX-OST-(*)-OST-M	\$37.50	2-prong	2-prong
HDX-OST-(*)-SMP-M	37.50	2-prong	Miniature
HDX-OST-U-PP2	37.50	2-prong	Phone Plug
HDX-OTP-(*)-OTP-M	37.50	3-prong	3-prong
HDX-OTP-U-PP3	37.50	3-prong	Phone Plug
HDX-OTP-U-TA3FL	37.50	3-prong	TA3F†

†Lead "1" is connected to red RTD prong, i.e., small diameter end prong. Other wiring available.

Ordering Example: SDX-UST-K-SMP-M, universal plastic handle for Type K with miniature connector on cable, \$25.  
HDX-OST-K-SMP-M, 2 prong miniature aluminum handle, \$37.50.

## SDX Plastic Handles

To Order (Specify Model Number)			
Model Number	Price	Connector in Handle	Connector on Cable
SDX-UST-(*)-OST-M	\$25	Universal—Accepts Standard and Mini. Sizes	2-prong
SDX-UST-(*)-SMP-M	25		Miniature
SDX-UST-U-PP2	25		Phone Plug

**MOST POPULAR MODELS HIGHLIGHTED!**

Note: Supplied with HDX aluminum handle for lengths over 600 mm (24"). Consult Sales for pricing.

\*Insert Calibration Code:  
**J** = Iron-Constantan      **K** = CHROMEPA®-ALOMEGA®  
**T** = Copper-Constantan    **E** = CHROMEPA®-Constantan  
**U** = Uncompensated Copper



#### UNITED STATES

[www.omega.com](http://www.omega.com)  
1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)  
Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)  
Deckenpfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)  
Manchester, England  
0800-488-488

#### FRANCE

[www.omega.fr](http://www.omega.fr)  
Guyancourt, France  
088-466-342

#### CZECH REPUBLIC

[www.omegaeng.cz](http://www.omegaeng.cz)  
Karviná, Czech Republic  
596-311-899

#### BENELUX

[www.omega.nl](http://www.omega.nl)  
Amstelveen, NL  
0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters