

Special Purpose Probes

Dual Thermocouple Probe with NPT Fitting

1/8" NPT SS fitting for installation into any standard pipe opening. Dual sensors with 1 m (40") leads and SMPW connectors.

MEETS OR EXCEEDS SPECIAL LIMITS OF ERROR (SLE) AND EN 60584-2: Tolerance Class 1

MADE IN USA



STS-2X, Solder Iron Measuring Module with Sensor Head Element
STS-H Replacement sensor, \$60.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)


Model Number	Price	Description
TC-(*)-NPT-G-36-DUAL-SMPW-M	\$60	Dual thermocouple 1/8" NPT
RTD-NPT-72-(†)-DUAL-MTP	115	Dual RTD 1/8" NPT
STS-2X	79	Solder iron module
FTP-(*)-2-SMP-M	120	Flow through probe

* Specify Type J, K, T, or E Thermocouple type † Specify "E" for 0.00385 or "A" for 0.00392 curve
** Other lengths are available, consult Sales Department

Ordering Example: FTP-K-2-SMP-M, Type K, flow through probe with 1/4" stainless steel fitting and SMPW write-on connector, \$120.

Dual RTD Probe with NPT Fitting

1/8" NPT SS fitting for installation into any standard pipe opening. Dual RTD sensor with flush sensing surface 1.8 m (72") leads and MTP connectors. Many other RTD probes are available; see eg: PR-11, PR-12 Series.



FTP Probe

Specially made to measure temperature in a 6 mm (1/4") diameter tube; 51 mm (2") stem protects connector from extreme environment of the pipe. Use in uncontaminated fluids. 304 stainless steel probe with 6 mm (1/4") diameter compression fittings on input and output flow ports.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters