



THERMOCOUPLE TERMINAL BLOCKS

XBTK Series Starts at £5.40



- Type J, K, T, E, R Terminal Blocks
- Screw Type Terminal Block DIN Connectors
- Maintenance-Free Connections
- Global Acceptance
- Large Surface Area for Marking

Thermocouple terminal blocks are offered in Type K, J, T, E and R. The terminal block contacts are made with thermocouple-grade calibration alloys. The terminal blocks come in a grey colour but white blank marker strips are available for identification.

SPECIFICATIONS

Terminal Width: 10.4 mm

Maximum Wire Size: 12 AWG/2.5 mm²

Connection Data in V/AWG: 400/24-12

UL-cUL Ratings in V/A/AWG: 300/10/28-12

Width/Length/Cover Width in mm: 5.2/46.0/1.0


Height for 35 x 7.5/35 x 15 in mm:

40.0/47.5/45.0

Stripping Length in mm: 7

Thread: M3

Torque in Nm: 5.3 to 7.1



All models shown larger than actual size.

To Order (Specify Model Number)

MOST POPULAR MODELS HIGHLIGHTED!

MODEL NO.	PRICE	DESCRIPTION
XBTKK25	£5.40	Type K thermocouple terminal block
XBTKJ25	5.40	Type J thermocouple terminal block
XBTKE25	5.40	Type E thermocouple terminal block
XBTKT25	5.40	Type T thermocouple terminal block
XBTKR25	5.40	Type R thermocouple terminal block

Ordering Example: XBTKK25, type K terminal block, XBACTK4-10PK, end covers, XBANS3575P, DIN rail, £5.40 + 3.80 + 6 = £15.20.

ACCESSORIES

MODEL NO.	PRICE	DESCRIPTION
XBACTK4-10PK	£3.80	Grey end cover, pack of 10
XBMZB10-10PK	3.10	White blank marker strip, pack of 10
XBANS3575P	6.00	DIN rail 35 x 7.5 mm x 2 m slotted
XBANS3575U	6.20	DIN rail 35 x 7.5 mm x 2 m solid
XBANS3515P	11.50	DIN rail 35 x 15 mm x 2 m slotted
XBANS3515U	11.50	DIN rail 35 x 15 mm x 2 m slotted
XBAES35C-50PK	28.00	1-screw mounted end stop, pack of 50
XBAES35T-50PK	21.00	3-screw mounted end stop, pack of 50
XBAES35N-50PK	17.75	Snap-on end stop, pack of 50

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA

Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)

1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenpfronn, Germany

0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England

0800-488-488

FRANCE

www.omega.fr

088-466-342

CZECH REPUBLIC

www.omegaeng.cz

Karviná, Czech Republic

596-311-899

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters