

FLOW MONITORS FOR CORROSIVE OR ULTRAPURE FLUIDS

CAPACITY: 0 to 8 GPM of Water

B

FL-X3
\$506




- ✓ ±5% Full Scale Accuracy
- ✓ ±1% Reading Repeatability
- ✓ Built-in Signal Switch
- ✓ 316SS Wetted Parts
- ✓ Designed for Use with Clear or Opaque Liquids
- ✓ Corrosion Resistant Construction
- ✓ Polysulfone Housing
- ✓ 200 psig Pressure Rating
- ✓ 93°C (200°F) Temperature Rating



FL-X5, \$506, shown smaller than actual size.

FL-X Series variable-area flowrate indicators utilize fluid movement to actuate a swinging vane, which drives the scale pointer and triggers the signal switch. The corrosion-resistant construction includes no breakable tubes, and a display that is unaffected by the opacity of the fluid.

These flowmeters feature rugged construction and easily accommodate flows up to 1.5 times the maximum scale reading without damage. All internal wetted parts are made of 316SS, and the body housing is polysulfone with Viton® seals.



MOST POPULAR MODEL HIGHLIGHTED!

To Order (Specify Model Number)			
Model No.	Price	Flow Range (GPM Water)	Readout Increments
FL-X3	\$506	0 to 3	1
FL-X4	506	0 to 4	1
FL-X5	506	0 to 5	1
FL-X6	506	0 to 6	1
FL-X7	506	0 to 7	1
FL-X8	556	0 to 8	1
FL-X9	556	0 to 8	1
CM-4339	115	Reference Book: Flow Measurement Methods and Applications	

SPECIFICATIONS

Accuracy: ±5% full scale

Repeatability: ±1% of reading

Pressure Drop: 2.2 psi, average

Weight: 794 g (1 lb, 12 oz)

Signal Switch: 3-Wire SPDT, Rated 15 A @ 125 Vac

Max. Pressure: 200 psig from -18 to 93°C (0 to 200°F)

Housing Material: Polysulfone

Internal Wetted Parts: 316SS

Seals: Viton®

Connections: ¾" NPT, Female, Plastic

Ordering Examples: FL-X8, flowmeter for corrosive or ultrapure fluids, 0 to 8 GPM range, \$556. FL-X3, flowmeter for corrosive or ultrapure fluids, 0 to 3 GPM range, \$506.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters