

LONG-LIFE PULSE OUTPUT WATER METERS

For Remote Rate Indication and Totalization

FTB4600 Series Starts at

\$173



- ✓ For Water Flows from 0.15 to 20 GPM
- ✓ Economical
- ✓ High Turndown Ratio
- ✓ Up to $\pm 1.5\%$ Rdg Accuracy

Designed for long-term water billing applications, the FTB4600 Series flowmeters are highly accurate and feature a high-frequency pulse output suitable for remote flow-rate indication or flow totalization. For economy, they have no local indication of the flow rate or total. The pulse output is compatible with OMEGA's DPF400 and DPF700 Series ratemeter/totalizers. All meters come with built-in strainers, locking nuts, gaskets, coupling pieces, and 1.5 m (5') of 3-conductor copper wire.

SPECIFICATIONS

Accuracy: From 10% of continuous to max flow: $\pm 1.5\%$ of rate; below 10% of continuous flow: 2% of rate

Fluid Temperature Range: 0 to 88°C (32 to 190°F)


Wetted Parts: Brass body, stainless steel, polyimide (fiberglass), polypropylene, EPDM O-ring

Pressure Drop (at Continuous Flow Rate): 2.9 psid

Max Pressure: 150 psig

Pulse Output: Requires 6 to 16 Vdc @ 10 mA max power; output requires pull-up to positive DC voltage; includes 1.5 m (5') of cable

Duty Cycle: 50-50



FTB4605 pulse output water meter, \$173, shown smaller than actual size.

Comes complete with built-in strainers, locking nuts, gaskets, coupling pieces, 1.5 m (5') cable and operator's manual.



DPF700 Series ratemeter/totalizer/ batch controller, \$260. See page M-5.

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)

Bronze Body

Model No.	Price	Port Size	Flow Rate (GPM)			Dimensions: mm (in)			Weight kg (lb)	Pulses per Gallon
			Min	Cont.	Max	Length	Height	Width		
FTB4605	\$173	1/2"	0.15	6.6	13.0	110 (4.3)	70 (2.75)	70 (2.75)	0.5 (1.1)	151.4
FTB4607	187	3/4"	0.22	11.0	20.0	130 (5.13)	73 (2.9)	70 (2.75)	0.6 (1.4)	75.7
FW-0119	155	Reference Book: Flow Measurement								

Comes complete with built-in strainers, locking nuts, gaskets, coupling pieces, 1.5 m (5') cable and operator's manual.

Ordering Examples: FTB4605, bronze body water meter, 1/2" port size, \$173.

FTB4607, bronze body water meter, 3/4" port size, \$187.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters