

THERMOPLASTIC QUICK COUPLINGS HIGH FLOW COUPLING

3/8" Flow Polysulfone, FT-HFC-35 Series
1/2" Flow Polysulfone, FT-FFC-35 Series

Applications


- High-Purity and Deionized water
- Filtration Equipment
- Pharmaceutical Equipment
- Heavy Equipment Cooling Lines
- Food and Beverage Serving Equipment
- Bioprocessing Lines
- Laboratory Equipment and Instrumentation

New FT-HFC-35 Series couplings are designed to withstand the rigors of demanding applications. Their polysulfone construction imparts physical strength, repeated autoclaving capability and chemical resistance. FT-HFC-35 Series couplings' attractive design, light weight and large capacity make them a perfect replacement in many applications for stainless steel or brass. Use FT-HFC-35 couplings anywhere—available in the most common thread and hose sizes, 3/4" NPT or garden hose for drum unloading, male and female thread connections. Special-order couplings are available in versions that comply with listing requirements for NSF standard C-2 as well as versions certified to meet USP Class VI requirements. Fully interchangeable with FT-HFC-12 Series couplings. Patent No. 5316041.

FT-HFC Series

\$13

Basic Model



Coupling Bodies 3/8" Flow

MOST POPULAR MODELS HIGHLIGHTED!



Male Pipe Thread Body					1/2" Flow FT-FFC			
MALE THREAD	STRAIGHT THRU MODEL NUMBER	PRICE	SHUTOFF MODEL NUMBER	PRICE	FULL FLOW MODEL NUMBER	PRICE	LENGTH	
3/8" NPT	FT-HFC106-35	\$13	FT-HFCD106-35	\$16	—	—	2.72"	
3/8" BS	FT-HFC106-35BS	13	FT-HFCD106-35BS	17	—	—	2.72"	
1/2" NPT	FT-HFC108-35	13	FT-HFCD108-35	16	FT-FFC108-35	\$13	2.72"	
1/2" BS	FT-HFC108-35BS	13	FT-HFCD108-35BS	16	—	—	2.72"	
3/4" NPT	FT-HFC1012-35	13	FT-HFCD1012-35	17	FT-FFC1012-35	14	3.07"	
3/4" BS	FT-HFC1012-35BS	13	FT-HFCD1012-35BS	17	FT-FFC1012-35BS	14	3.07"	
3/4" GdnHs	FT-HFC1012-35GH	13	FT-HFCD1012-35GH	16	FT-FFC1012-35GH	14	2.94"	

In Line Hose Barb Body					1/2" Flow FT-FFC			
TUBING SIZE ID	METRIC EQ MM	STRAIGHT THRU MODEL NUMBER	PRICE	SHUTOFF MODEL NUMBER	PRICE	FULL FLOW MODEL NUMBER	PRICE	LENGTH
3/8"	9.5	FT-HFC176-35	\$13	FT-HFCD176-35	\$16	—	—	2.82"
1/2"	12.7	FT-HFC178-35	13	FT-HFCD178-35	16	—	—	2.82"
3/4"	19	FT-HFC1712-35	14	FT-HFCD1712-35	17	FT-FFC1712-35	\$14	2.97"

Bulkhead Panel Mount Hose Barb Body					1/2" Flow FT-FFC			
TUBING SIZE ID	METRIC EQ MM	STRAIGHT THRU MODEL NUMBER	PRICE	SHUTOFF MODEL NUMBER	PRICE	FULL FLOW MODEL NUMBER	PRICE	LENGTH
3/8"	9.5	FT-HFC166-35	\$17	FT-HFCD166-35	\$21	—	—	2.82"
1/2"	12.7	FT-HFC168-35	17	FT-HFCD168-35	21	—	—	2.82"
3/4"	19	FT-HFC1612-35	17	FT-HFCD1612-35	21	FT-FFC1612-35	\$18	2.97"

Female Pipe Thread Body					1/2" Flow FT-FFC			
FEMALE THREAD	STRAIGHT THRU MODEL NUMBER	PRICE	SHUTOFF MODEL NUMBER	PRICE	FULL FLOW MODEL NUMBER	PRICE	LENGTH	
3/4" GdnHsMt	FT-HFC1912-35BP	\$15	FT-HFCD1912-35BP	\$19	FT-FFC1912-35BP	\$15	2.69"	
3/4" GdnHs	FT-HFC1912-35GH	15	FT-HFCD1912-35GH	18	FT-FFC1912-35GH	15	2.69"	

Panel thickness .030" to 0.25", 1.20" diameter mounting hole 1.87" minimum coupling spacing Greenlee 730K-3/16 Keyway Punch Unit and 730S Hole Punch.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters