


# OMEGAFLEX® Chemical Tubing PTFE FORMULATION

TYTT-42-50

**\$55**

50' Spool



Think of OMEGA for Specialty Tubing!

- ✓ Coiled
- ✓ Kevlar® Wrapping
- ✓ Plastic and Metal Overbraiding
- ✓ Flexible Styles
- ✓ Custom Lengths



**ALL MODELS AVAILABLE FOR FAST DELIVERY!**

## To Order (Specify Model Number)

4 to 16 mm OD TUBING, METRIC DIAMETERS

Model No.	Price	Std Length (ft)	Wall (mm)	OD (mm)	ID (mm)	psi @73°F
TYTT-42-50	\$55	50	1	4	2	320
TYTT-42-100	110	100	1	4	2	320
TYTT-64-50	85	50	1	6	4	210
TYTT-64-100	170	100	1	6	4	210
TYTT-86-50	144	50	1	8	6	160
TYTT-86-100	208	100	1	8	6	160
TYTT-108-25	100	25	1	10	8	125
TYTT-108-50	200	50	1	10	8	125
TYTT-108-100	400	100	1	10	8	125
TYTT-1210-25	110	25	1	12	10	105
TYTT-1210-50	220	50	1	12	10	105
TYTT-1210-100	440	100	1	12	10	105
TYTT-1412-25	130	25	1	14	12	90
TYTT-1412-50	260	50	1	14	12	90
TYTT-1412-100	520	100	1	14	12	90
TYTT-1614-25	160	25	1	16	14	80
TYTT-1614-50	320	50	1	16	14	80
TYTT-1614-100	640	100	1	16	14	80

Field testing is recommended to find the actual operating specifications in the given application.

**Note:** TFE is translucent white.

Sold in standard lengths of 25, 50, and 100'. TFE is coiled in 25' no-splice package, 50' maximum 2-splice package or 100' maximum 3-splice package.

**Ordering Example:** TYTT-1412-100, 100' of tubing, 1 mm wall, 14 mm OD, 12 mm ID, \$520.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters