

LABORATORY HEATING MANTLES

LHM Series
Starts at
\$174

PERFORMANCE CAPABILITIES

- ✓ Temperature Ratings to 482°C (900°F)
- ✓ Low Watt Density
- ✓ Uniform Heat Distribution

FEATURES

- ✓ Custom Designs Available
- ✓ Molded to Fit Flask




LABORATORY SAMPLE HEATERS

OEM applications often require heating for various laboratory glassware and apparatuses in chromatographic and spectrographic analyses. OMEGA® serves these needs with custom heaters designed to meet the user's requirements.

LABORATORY HEATING MANTLES

OMEGA's heating mantles offer uniform heat distribution for round-bottom flasks. Whether the need is a self-standing mantle, a mantle to fit in a basket ring stand, or a full-coverage zippered mantle, OMEGA® has the solution.



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

Model No. 120 Vac	Price	Model No 240 Vac	Price	Size mL	Total Watts
LHM-0050-VF1	\$174	LHM-0050-VF2	\$174	50	52
LHM-0100-VF1	192	LHM-0100-VF2	192	100	70
LHM-0250-VF1	205	LHM-0250-VF2	205	250	143
LHM-0500-VF1	231	LHM-0500-VF2	231	500	210
LHM-1000-VF1	378	LHM-1000-VF2	378	1000	377
LHM-2000-VF1	406	LHM-2000-VF2	406	2000	520
LHM-3000-VF1	435	LHM-3000-VF2	435	3000	550
LHM-5000-VF1	509	LHM-5000-VF2	509	5000	620

120V models come with a 1.8 m (6') power cord with a 2 P, 2 W straight-blade plug.
240V models come with a 1.8 m (6') power cord with a 2 P, 3 W straight-blade plug.
Ordering Example: LHM-0050-VF1, 50 mL, 52 W heating mantle, \$174.

Tabletop Heating Mantles 482°C (900°F) Continuous

TABLETOP HEATING MANTLES

are self-supporting mantles that can be placed directly on a countertop or stacked for easy storage. Tabletop mantles permit easy viewing of the flask contents.

N

LABORATORY HEATING MANTLES

Spherical Heating Mantles 450°C (842°F) Continuous

LHMSS1 Series
Starts at


\$198

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)						
Model No. 120 Vac	Price	Model No. 240 Vac	Price	Size mL	Total Watts	
					Upper	Lower
LHM0500-SS1	\$198	LHM0500-SS2	\$198	500	077	270
LHM1000-SS1	345	LHM1000-SS2	345	1000	140	380
LHM2000-SS1	377	LHM2000-SS2	377	2000	200	500

Comes with complete operator's manual. 120V power cords are 15 cm (6") long with a 2-pole twist-lock power connector and are supplied with a 1.2 m (4') power adaptor cord with a 2 P, 2 W straight-blade plug. 240V power cords are 15 cm (6") long with no plug.

Ordering Example: LHM1000-SS1, 120V, 1000 mL heating mantle, \$345.



Upper Hemispherical Heating Mantles 450°C (842°F) Continuous

LHMST Series
Starts at


\$121

ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)					
Model No. 120 Vac	Price	Model No. 240 Vac	Price	Size mL	Total Watts
LHM0250-TS1	\$121	LHM0250-TS2	\$121	250	140
LHM0500-TS1	130	LHM0500-TS2	130	500	140
LHM1000-TS1	143	LHM1000-TS2	143	1000	140
LHM2000-TS1	162	LHM2000-TS2	162	2000	20
LHM3000-TS1	162	LHM3000-TS2	162	3000	20
LHM5000-TS1	216	LHM5000-TS2	215	5000	300

Comes with complete operator's manual. 120V power cords are 15 cm (6") long with a 2-pole twist-lock power connector and are supplied with a 1.2 m (4') power adaptor cord with a 2 P, 2 W straight-blade plug. 240V power cords are 15 cm (6") long with no plug.

Ordering Example: LHM0250-TS1, 120V, 250 mL heating mantle, \$121.



UPPER HEMISPHERICAL MANTLES are ideal for preventing vapor condensation in the upper half of the flask. The opening holds 1-, 2-, or 3-neck flasks.

LABORATORY HEATING MANTLES




Lower Hemispherical Heating Mantles 450°C (842°F) Continuous

LHMHS Series
Starts at

\$168

UPPER HEMISPHERICAL HEATING MANTLES

are the same as the lower half of the spherical mantles, but without the zipper. These mantles are ideal for use with a basket ring and permit easy viewing of the flask contents.



ALL MODELS AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model No.)					
Model No. 120 Vac	Price	Model No. 240 Vac	Price	Size mL	Total Watts
LHM0050-HS1	\$168	LHM0050-HS2	\$168	50	60
LHM0100-HS1	188	LHM0100-HS2	188	100	80
LHM0125-HS1	191	LHM0125-HS2	191	125	80
LHM0200-HS1	196	LHM0200-HS2	196	200	100
LHM0250-HS1	199	LHM0250-HS2	199	250	180
LHM0500-HS1	206	LHM0500-HS2	206	500	270
LHM1000-HS1	239	LHM1000-HS2	239	1000	380
LHM2000-HS1	269	LHM2000-HS2	269	2000	500
LHM3000-HS1	300	LHM3000-HS2	300	3000	500
LHM5000-HS1	373	LHM5000-HS2	373	5000	600
LHM12000-HS1	746	LHM12000-HS2	746	12,000	1300

Comes with complete operator's manual. 120V power cords are 15 cm (6") long with a 2-pole twist-lock power connector and are supplied with a 1.2 m (4') power adaptor cord with a 2 P, 2 W straight-blade plug. 240V power cords are 15 cm (6") long with no plug.
Ordering Example: LHM0200-HS1, 120V, 200 mL heating mantle, \$196.

N

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters