


SILICON RUBBER HEATERS



Square/Rectangular SRMU Heat Blankets 9 to 12" Width



To Order (Specify Model Number)						
Width cm (")	Length cm (")	2.5Watts/in ² (0.39 Watts/cm ²)	5Watts/in ² (0.78 Watts/cm ²)	10 Watts/in ² (1.55 Watts/cm ²)	Price no PSA	Price with PSA*
22.86 (9)	22.86 (9)	SRMU020909	SRMU050909	SRMU100909	\$37.10	\$40.80
22.86 (9)	25.40 (10)	SRMU020910	SRMU050910	SRMU100910	39.20	43.10
22.86 (9)	27.94 (11)	SRMU020911	SRMU050911	SRMU100911	41.30	45.50
22.86 (9)	30.48 (12)	SRMU020912	SRMU050912	SRMU100912	43.50	47.80
25.40 (10)	25.40 (10)	SRMU021010	SRMU051010	SRMU101010	41.30	42.90
25.40 (10)	27.94 (11)	SRMU021011	SRMU051011	SRMU101011	43.50	47.80
25.40 (10)	30.48 (12)	SRMU021012	SRMU051012	SRMU101012	45.60	50.10
25.40 (10)	45.72 (18)	SRMU021018	SRMU051018	N/A	58.30	64.10
25.40 (10)	60.69 (24)	SRMU021024	SRMU051024	N/A	71.00	78.10
25.40 (10)	76.20 (30)	SRMU021030	SRMU051030	N/A	83.70	92.10
25.40 (10)	91.44 (36)	SRMU021036	SRMU051036	N/A	96.50	106.10
25.40 (10)	106.68 (42)	SRMU021042	N/A	N/A	109.20	120.10
25.40 (10)	121.92 (48)	SRMU021048	N/A	N/A	120.80	132.90
27.94 (11)	27.94 (11)	SRMU021111	SRMU051111	SRMU101111	45.60	50.10
27.94 (11)	30.48 (12)	SRMU021112	SRMU051112	SRMU101112	48.80	53.60
30.48 (12)	20.32 (12)	SRMU021212	SRMU051212	N/A	50.90	56.00
30.48 (12)	22.86 (18)	SRMU021218	SRMU051218	N/A	65.70	72.30
30.48 (12)	25.40 (24)	SRMU021224	SRMU051224	N/A	80.60	88.60
30.48 (12)	27.94 (30)	SRMU021230	N/A	N/A	96.50	106.10
30.48 (12)	30.48 (36)	SRMU021236	N/A	N/A	111.30	122.40
30.48 (12)	45.72 (42)	SRMU021242	N/A	N/A	126.10	138.10
30.48 (12)	60.96 (48)	SRMU021248	N/A	N/A	141.00	155.10

* To order with PSA (Pressure Sensitive Adhesive) add suffix "-P" to Model Number.

To custom order 96" leads, add suffix "-096" to model number and \$45 to price.

Ordering Example: SRMU020608-P, 2.5 watt/in² 6 x 8" heater, \$33.80.

Silicon Rubber Enclosed Heaters


SREH series enclosure heaters feature our serpentine wound heating element laminated between two layers of 15 mil fiberglass reinforced silicone rubber and bonded to an aluminum mounting

plate. The mounting plate comes with two 11mm (7/16") holes for mounting. The built-in air sensing thermostat regulates the temperature in the enclosure to prevent condensation or

freezing. The SREH enclosure heaters can be mounted vertically or horizontally, however optimal control is achieved when mounted vertically.

- ✓ Moisture resistant
- ✓ Chemical resistant
- ✓ Radiation resistant

Approvals:
UR pending



To Order (Specify Model Number)						
Width cm (")	Length cm (")	Total Watts	Thermostat		Model Number (120VAC)	Price
			Opens	Closes		
6.4 (2.5)	15.24 (6)	60	N/A	N/A	SREH600	\$24
6.4 (2.5)	15.24 (6)	60	15°C (60°F)	4°C (40°F)	SREH640	76
6.4 (2.5)	15.24 (6)	60	60°C (140°F)	43°C (110°F)	SREH6110	76
6.4 (2.5)	15.24 (6)	60	82°C (180°F)	65°C (150°F)	SREH6150	76
6.4 (2.5)	30.48 (12)	120	N/A	N/A	SREH1200	31
6.4 (2.5)	30.48 (12)	120	15°C (60°F)	4°C (40°F)	SREH1240	84
6.4 (2.5)	30.48 (12)	120	140°F (60°C)	43°C (110°F)	SREH12110	84
6.4 (2.5)	30.48 (12)	120	180°F (82°C)	65°C (150°F)	SREH12150	84

Ordering Example: SREH1240, 30.48 cm (12"), 120 Watt heater with 15°C (60°F) setpoint thermostat, \$84.00

M-8D

SPECIFICATIONS

Operating Voltage: 120 Vac

Leads: 122 cm (48") Teflon

Heating Element:

laminated between two layers of, 0.015 mil, fiberglass reinforced silicone rubber

Silicone Rubber Density: 16.8 oz/yd² (0.06 grams/cm²) per layer

Overall Thickness: (blanket and bracket) 1/4" (0.64 cm)

Maximum Energized Exposure

Temperature: 232°C (450°F)

Maximum De-energized

Exposure Temperature: 260°C (500°F)

Minimum Exposure

Temperature: -51°C (-60°F)

Dielectric Strength: > 2000 volts



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters