

SSRL SERIES PUMP-UP/PUMP-DOWN RELAYS

With Latching Capability



SSRL2, \$99, shown actual size.

SSRL Series Starts at **\$99**



The SSRL Series are latching 5 amp SPST NO relays with a small output current to sense the closing of up to two dry mechanical relay contacts. They are ideal for differential level control for pump-up or pump-down applications when combined with any two level switches with dry relay contact closures, such as 2 LV-10 switches or 2 LV-230 switches, for example. The SSRL relays also convert non-latching mechanic relay outputs into latching alarm outputs, or allow low power reed relay switches to control high amperage or high voltage devices, such as pumps or motors. Latching operation is reset by making a momentary contact between the COM and OFF terminals. The SSRL holds its operational state for up to 1/2 second during momentary power loss to avoid nuisance shutdowns. A short between the COM and OFF terminals shuts the relay off, regardless of the switch status at the ON terminal.

SPECIFICATIONS

- Load Side Voltage Loss:** 2 Vac
- Maximum Relay Closure Sense Current/Voltage:** 20 mA @ 11 Vdc nominal
- Minimum Load:** 10 times the leakage current
- Leakage Current Through Load Terminals:** 2 mA at 120 Vac; 4 mA at 240 Vac
- Housing Material:** Polysulfone



SSRL3, \$140, shown smaller than actual size.

The SSRL Series Relays are not failsafe; we recommend a third level switch independent of the SSRL for alarm of overfill or overdrain conditions.

AVAILABLE FOR FAST DELIVERY

To Order (Specify Model Number)		
Model No.	Price	Description
SSRL2	\$99	Switches 100 to 130 Vac loads, 50/60 Hz
SSRL3	140	Switches 200 to 250 Vac loads, 50/60 Hz

Comes complete with operator's manual.

Ordering Example: SSRL-2, relay to switch, 100 to 130 Vac loads, \$99.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters