

Event Recorders

CT87E Series
Starts at
\$303



- 152 mm (6") Chart With 0.5" LED
- 4 Voltage/Current or 3 Event Modes
- 4 Recording Speeds
- All Front Panel Selectable
- Single or Continuous Chart Rotation
- Free Standing or Wall Mount

The CT87V is a precision instrument used to monitor and record voltage or current on a 152 mm (6") circular paper chart. A 3-digit LED displays the value. The CT87E is a highly versatile instrument, accurately records voltage, light or sound events. LED display can read length of events, time between events or total number of events. Battery backup assures normal operation during power interruptions. The unit can also be run from any 12 Vdc source (auto or marine).



Ambient Operating Temperature: 0 to 60°C (32 to 140°F)
Ambient Operating Relative Humidity: 96% maximum
Primary Power Supply: 120 Vac, 50/60 Hz (220 to 240 Vac, 50/60 Hz optional)
Battery Backup: 8 "AA" alkaline batteries (included)

CT87E, \$303, shown smaller than actual size. CT87V appearance is similar, except offers a 4 position range switch.

Battery Life: 48-hr continuous use
Recording Pen: Ink type
Case Size: 235 x 184 x 70 mm (9 1/4 x 7 1/4 x 2 3/4")
Weight: 2.13 kg (4 lb, 7 oz)
Case Material: Polycarbonate

MOST POPULAR MODELS HIGHLIGHTED!

Specifications

CT87V Model Range (Accuracy):
 0 to 5.00 (± 0.01 V); 0 to 100 mV (± 1 mV)
 0 to 20.0 mA (± 0.1 mA), 4 to 20.0 mA (± 0.1 mA)

CT87E Model Event Probes:

- a) **Volt:** 2 wire clip leads for 24 to 270 Vac (50/60 Hz) or 24 to 180 Vdc
- b) **Light:** A sensitive photo cell for 18 to 1900 lux $\pm 20\%$
- c) **Sound:** A sensitive audio transducer for 40 to 114 dB @ 1 kHz $\pm 20\%$ thresholds

Chart Speed Selectable:

6-hr, 24-hr, 7-day, 31-day

Chart Rotation Mode: Selectable, single turn or continuous

Chart Speed Accuracy: $\pm 1\%$

Chart Diameter: 152 mm (6")

Display: 3-digit 13 mm (0.5") LED to display event interval in minutes, length of the event in minutes, and/or total number of events for CT87E or voltage/current value for CT87V

To Order (Specify Model Number)

Model No.	Price	Description
CT87V	\$302	Circular voltage/current recorder
CT87V-230	324	Circular voltage/current recorder, 230 Vac
CT87E	303	Circular event recorder
CT87E-230	314	Circular event recorder, 230 Vac
CT87EV-RP	35	Replacement voltage sensor
CT87EL-RP	35	Replacement light sensor
CT87ES-RP	35	Replacement sound sensor
CT87-PEN-BLACK	8.50	Replacement pen
CT87V-C-(*)	19.25	Charts (60 pcs) for CT87V
CT87C-(*)	19.25	Charts (60 pcs) for CT87E
MN1500	1.75	AA batteries (pack of 2)

* Insert chart rotation code: "6H" for 6 hours, "24H" for 24 hours, "7D" for 7 days, or "31D" for 31-days. Each unit supplied with 8 "AA" alkaline batteries, AC adaptor, 2 pens, 60 assorted charts, and operator's manual. CT87E also includes 3 sensors (volt, light, and sound). OMEGACARESM extended warranty program is available for models shown on this page. OMEGACARESM covers parts, labor, and equivalent loaners. Ask your sales representative for full details when placing an order.

Ordering Example: CT87E, 152 mm (6") circular event recorder, \$303. OCW-3, OMEGACARESM extends standard 1-year warranty to a total of 4 years (\$75), \$303 + 75 = \$378.



UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters