

OMEGAETTE™

Economical Multimeters with High Performance Features

HMM90 Series
Starts at
\$29



- ✓ Large 3½ or 3¾ Display
- ✓ AC/DC Current
- ✓ Resistance Measurement
- ✓ Capacitance Measurement
- ✓ Continuity Check Feature



- Full Function Multimeter**
- ✓ 3½ Digit Big Display
 - ✓ HFE Test Function
 - ✓ Capacitance Measurement
 - ✓ Audible Continuity Check Function

HMM95 multimeter full function, \$61, shown smaller than actual size.

3½ Digit Display
(2000 Counts).



HMM93 multimeter/transistor tester, \$29, shown smaller than actual size.

Cheaper by the Dozen!
Order Model HMM93-12 \$290.

Good for Transistor Testing/Measure HFE and Transistor Junctions

- ✓ 3½ Digit Big Display
- ✓ Diode Test Function
- ✓ HFE Test Function




HMM93B multimeter \$36, shown smaller than actual size.

Cheaper by the Dozen!
Order Model HMM93B-12 \$360.

Multimeter with High Performance Features

- ✓ 3½ Digit Big Display
- ✓ Diode Test Function
- ✓ Continuity Check Feature
- ✓ HFE Test Function



HHM97EL digital/analog bargraph multimeter with backlight, \$82, shown smaller than actual size.

HHM97 digital/analog bargraph multimeter, \$66, shown smaller than actual size.

- ✓ 3¾ Digit Backlit Display
- ✓ Analog/Digital Readout
- ✓ Auto/Manual Operation
- ✓ Auto Power-Off Feature

- ✓ 3¾ Digit Display
- ✓ Analog/Digital Readout
- ✓ Auto/Manual Operation
- ✓ Auto Power OFF Feature

All Units Come with Rubber Boot and Test Leads.

Specifications

Model No.		HHM93	HHM93B	HHM95	HHM97	HHM97EL
DC Voltage	Accuracy	± (0.5% rdg + 2 dgts)			± (1.0% rdg + 2 dgts)	
	Ranges	2/20/200/600 V			320m/3.2/32/320/600 V	
AC Voltage	Accuracy	±(1.5% rdg + 5 dgts)			±(2.5% rdg + 5 dgts)	
	Ranges	200/600 V		20/200/600 V	3.2/32/320/600 V	
DC Current	Accuracy	± (1.5% rdg + 3 dgts) for mA ± (2.0% rdg + 4 dgts) for 10 A			± (2.0% rdg + 3 dgts) for mA ± (3.0% rdg + 4 dgts) for 10 A	
	Ranges	2 m/20 m/200 m/10 A		20 m/10 A	32 m/320 m/10 A	
AC Current	Accuracy	–			± (2.0% rdg + 5 dgts) for mA ± (3.0% rdg + 5 dgts) for 10 A	
	Ranges	–			20 m/10 A	32m/320m/10 A
Resistance	Accuracy	± (1.0% rdg + 3 dgts) ± (2.5 % rdg + 5 dgts) for 20 MΩ			± (1.5% rdg + 3 dgts) ± (5.0% rdg + 7 dgts) for 32 MΩ	
	Ranges	200/2 k/20 k/200 k/2 MΩ		200/2 k/20 k/ 200 k/2 M/20 MΩ	320/3.2 k/32 k/ 320 k/3.2 M/32 MΩ	
Capacitance	Accuracy	–			± (3.0% rdg + 10 dgts)	
	Ranges	–			2 n/20 n/200 n/2 μ/20 μF	
HFE test		Yes		Yes	No	

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)		
Model No.	Price	Description
HHM93	\$29	Multimeter/transistor tester
HHM93-12	290	12 multimeter/transistor testers
HHM93B	36	High performance multimeter
HHM93B-12	360	12 high performance multimeters
HHM95	61	Full function multimeter
HHM97	66	Multimeter with bargraph
HHM97EL	82	Multimeter with bargraph and backlight
HHM-NIST	55	NIST calibration certificate

Comes with rubber boot, 9 V battery, test leads and operator's manual. **Ordering Example: HHM97EL, multimeter with bargraph and backlight, \$82.**

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters