

600V FAST ACTING FUSES



**HCLR Series
Starts at
\$60
Pkg of 10**



- Fast Acting 600V Fuse
- Compact Design
- High Interrupt Rating
- 0.5 to 30 A Rating
- Class CC Fuse

A fast acting, high-interrupt capacity, current limiting type fuse. The HCLR style fuse provides an excellent choice for applications such as: lighting and resistive heating loads.

SPECIFICATIONS

Dimensions: 1/2" ferrule, 38 mm (1.5") length

Weight: Approx 3.2 oz (0.2 lb)

Voltage Rating: HCLR-600 Vac

Ampere Rating: 0.1 to 30 A

Interrupting Rating: 200k RMS Amps

Current Limiting: Class CC Fuse

Agency Approvals: UL Listed, Class CC, Guide JDDZ, File E162363; CSA Certified HCLR-MISC per C22.2, No.248.4



HCLR5-10PK, \$60, shown actual size.

To Order (Specify Model Number)

MOST POPULAR MODELS HIGHLIGHTED!

MODEL NO.	PRICE PKG OF 10	AMPERAGE	MODEL NO.	PRICE PKG OF 10	AMPERAGE
HCLR.5-10PK	\$64	0.5	HCLR6-10PK	\$63	6
HCLR.75-10PK	69	0.75	HCLR7-10PK	74	7
HCLR1-10PK	60	1.0	HCLR8-10PK	64	8
HCLR1.5-10PK	60	1.5	HCLR9-10PK	81	9
HCLR2-10PK	60	2.0	HCLR10-10PK	60	10
HCLR2.5-10PK	78	2.5	HCLR12-10PK	61	12
HCLR3-10PK	60	3.0	HCLR15-10PK	60	15
HCLR3.5-10PK	81	3.5	HCLR20-10PK	60	20
HCLR4-10PK	64	4.0	HCLR25-10PK	64	25
HCLR5-10PK	60	5.0	HCLR30-10PK	60	30

Ordering Examples: HCLR5-10PK, 600V fast acting fuses with 5 A rating, package of 10, \$60.
HCLR.75-10PK, 600V fast acting fuses with 0.75 A rating, package of 10, \$69.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters