

# OMG-ULTRA-COMM232-PCI

## Dual Port PCI RS-232 Interface for DOS and Windows 3.1x/95/98/ME/NT/2000/XP

**\$189**  
Basic Model




- Dual Port RS-232 Interface
- Each Port Designed to Maximize DOS and WIN .1x/95/98/ME/NT/2000/XP Communications
- 16550 Buffered UART std/16650 or 16750 Buffered UART Optional (32 or 64 byte FIFO)
- Supports Standard PC Data Rates and "Quad" Data Rates up to 460.8K bps
- Supports all PCI Interrupts
- Onboard Interrupt Status Port Provides Efficient Interrupt Sharing
- Compatible with DOS, WIN 95/98/ME/NT/2000, XP and Other Operating Systems
- DOS Utilities, Windows Advanced COM; Drivers, and Help Files are Included to Simplify Installation

The OMG-COMM232-PCI provides two RS-232 serial ports for control and automation applications.

The onboard interrupt status port provides maximum Windows flexibility.

The OMG-COMM232-PCI includes the 16550 UART, providing a 16 byte FIFO to keep your datacom applications running error free.



OMG-COMM232-PCI, \$189, shown smaller than actual size

The 16650 UART, featuring a 32 byte FIFO and the 16750 UART, offering a deep 64 byte FIFO are optional for high speed applications. Windows 3.1x drivers are optionally available for more than 4 COM

### Software

WIN 95/98/ME/NT/2000/XP drivers are included as well as support for Linux, QNX and DOS. The drivers provide IRQ sharing, advanced UART support and serial diagnostic utilities.

### Specifications

- Communications Chip:** 16550 (16650 and 16750 optionally)
- Number of Ports:** Two RS-232
- Max. Data Rate:** 460.8K bps
- Max. Data Distance:** Up to 50'
- Operating Temperature:** 0 to 122°F (0 to 50°C)
- Storage Temperature:** -4 to 158°F (-20 to 70°C)
- Humidity Range:** 10 to 90% RH
- Current Specifications:** +5 V @ 240 mA, +12 V @ 30 mA, -12 V @ 50 mA
- Connector(s):** (2) DB-9P
- Physical Dimensions:** 5.0 x 4.2" (12.70 x 10.67 cm)

**ALL MODELS AVAILABLE FOR FAST DELIVERY!**

To Order (Specify Model Number)		
Model No.	Price	Description
OMG-COMM232-PCI	\$189	Dual port RS-232 interface
OMG-COMM232-PCI-SS	203	Dual port RS-232 interface with 16650 UART upgrade
OMG-COMM232-PCI-SX	209	Dual port RS-232 interface with 16750 UART upgrade

Comes with complete operator's manual and serial utility disk.

**Ordering Example:** OMG-COMM232-PCI Dual port RS-232 interface and OMEGACARE™ 1-year extended warranty (adds 1 year to standard 1-year warranty), \$189 + 25 = \$214.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters