




# OMG-COMM4-LPCI

## Low Profile PCI 4-Port RS-232 Board



OMG-COMM4-LPCI-DB9, \$229, Shown smaller than actual size

**\$229**  
All Models



- ✓ 16C864 Buffered UART with 128-byte FIFOs
- ✓ Data Rates to 460.8K bps
- ✓ MD1 Low Profile and Universal Bus (3.3 V and 5 V) Compatible
- ✓ All Modem Control Signals Implemented
- ✓ Includes 1 m (3') Cable that Terminates to Four DB25M Connectors

The OMG-COMM4-LPCI-DB25 Low Profile PCI serial interface provides four RS-232 serial ports, each capable of data rates to 460.8K bps. Each RS-232 port implements all modem control signals for maximum compatibility with a wide range of peripherals. The board is MD1 Low Profile and Universal Bus (3.3 V and 5 V) compatible and utilizes a 16C864 UART to provide 128-byte Tx/Rx FIFOs for maximum reliability in data intensive applications. The board ships with a 36" cable that terminates to four DB25M connectors. If you need DB9 connectors, order the OMG-COMM4-LPCI-DB9 which includes a cable that terminates to four DB9M connectors.

The OMG-COMM4-LPCI-DB25 is for use in Low Profile PCI slots only. If you have a standard size PCI slot order the OMG-COMM4-PCI-DB25. These boards are compatible with Windows 98/2000/XP and Linux.

### Specifications

**Number of Ports:** 4  
**Communications Chip:** 16C864  
**Max Data Rate:** 460.8K bps  
**Max Data Distance:** 15.2 m (50')  
**Operating Temperature:** 0 to 70°C (32 to 158°F)  
**Storage Temperature:** -50 to 105°C (-58 to 221°F)  
**Humidity Range:** 10 to 90% RH  
**Dimensions:** 64 W x 119 mm L (2.5 x 4.7")  
**Weight:** 45 g (1.6 oz)

**MOST POPULAR MODELS HIGHLIGHTED!**

### To Order (Specify Model Number)

Model Number	Price	Description
OMG-COMM4-LPCI-DB25	\$229	LPCI 4-port RS-232 board with DB25 connectors (DB25 cable included)
OMG-COMM4-LPCI-DB9	229	LPCI 4-port RS-232 board with DB9 connectors (DB9 cable included)
OMG-COMM4-PCI-DB25	229	PCI 4-port RS-232 board with DB25 connectors (DB25 cable included)
OMG-COMM4-PCI-DB9	229	PCI 4-port RS-232 board with DB9 connectors (DB9 cable included)

Each unit supplied with utility software, 1 m (3') cable that Terminates to Four DB25M connectors and complete operator's manual on CD.  
**Ordering Example:** OMG-COMM4-LPCI-DB9 low profile PCI 4-port RS-232 board with DB9 connectors (DB9 cable included) and OMEGACARE<sup>SM</sup> 1 year extended warranty for the OMG-COMM4-LPCI-DB9 (adds 1 year to standard 1 year warranty), \$229 + 25 = \$254.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters