



Chlorine Analyzer

CLH-1740
\$169



- ✓ Read Total Chlorine from 0.01 to 10.00 ppm with 0.01 ppm Resolution
- ✓ Readings are Not Affected by Sample Color or Turbidity
- ✓ Extra Bold Display Includes an Analog Bar Graph Feature
- ✓ Memory Saves Calibration Values and Can Store up to 15 Readings
- ✓ Chlorine and pH Modes Also Displays Sample Temperature
- ✓ Waterproof Design With Matte Finish Makes Opening Battery Compartment and Changing Probe Tips Easier
- ✓ Automatic Shut-Off and Low Battery Indicator Provide User Convenience; Batteries (Included)
- ✓ Includes 100 Reagent Tablets at Almost Half the Price of Similar Chlorine ISE Reagents
- ✓ Follows EPA Protocol for ISE Methods

For your next chlorine analysis!

The world's first pocket-sized ISE meter for measuring chlorine directly in parts per million. It can also be used to display sample temperature or test for pH and ORP. The unit includes 100 reagent tablets at almost half the price of similar Chlorine ISE reagents. Interchangeable flat surface sensor modules make this the most versatile pocket tester ever offered.

Specifications

Display: Multifunction display with bar graph

Operating Conditions: 0 to 50°C (32 to 122°F) and <80% RH

Chlorine Range: 0.01 to 10.00 ppm (Total Chlorine)

Chlorine Accuracy: ± (10% of reading + 0.01 ppm) from 0.05 to 10.00 ppm

Temperature Range: -5 to 90°C (23 to 194°F)

Temperature Resolution: 0.1° to 99.9°, then 1°

Temperature Accuracy: ± 1°C (1.8°F) from -5 to 50°C (23 to 122°F), 3°C (±5.4°F) from 50 to 90°C (122 to 194°F)

Measurement Storage: 15 readings can be stored and recalled

Low Battery Indication: "BAT" appears on the display

Power: Four 1.55V PH-BATT-3 button batteries (included)

Auto Power Off: After 10 minutes of inactivity

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
CLH-1740	\$169	Chlorine analyzer
CLE-1732	99	Chlorine module 0.01 to 10.00 ppm/ ±10% of reading
PHE-1733	39	pH module
ORE-1742	49	ORP module
CLH-1746	15	Optional weighted stand and 5 sample cups
CLH-7044J	31	Chlorine reagent refill pack (100 tablets)
CLH-7045	18	24 pack of sample cups
PH-BATT-3	3	1.55V replacement battery (4 required)

Comes complete with 100 reagent tablets, chlorine module, four 1.55V batteries, tablet crusher, one sample cup with cap, and operator's manual.

Ordering Example: CLH-1740, chlorine analyzer, \$169.



CLH-1740, \$169, comes complete with 100 reagent tablets, CLE-1732 chlorine module, tablet crusher, one sample cup with cap, and batteries.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters