



FLOW ALERT SINGLE SENSOR CONTROLLER (ac)

FLCN-101
\$235



- ✓ **Calls Immediate Attention to Alarm Conditions**
- ✓ **High Intensity Strobe Light Reduces Operator Error**
- ✓ **Adjustable Time Delay Relay**
- ✓ **Controls Pumps, Valves and Alarms**
- ✓ **LED Displays Switch, Sensor and Relay Status**

FLCN-101, \$235, shown larger than actual size.



OMEGA's flow alert calls attention to alarm conditions. For operator alert to low flow conditions, the flow alert offers an excellent solution to this problem. An amber lens distributes the high intensity strobe light in a pattern which calls immediate attention to alarm conditions. The visual alert combined with a controller makes it both cost effective and easy to install.



SPECIFICATIONS

Voltage Input: Selectable, 120 or 240 Vac, 50 to 60 Hz.

Max Consumption: 5 watts

Lighting Element: High intensity lamp

Brightness: Greater than 50,000 CP

Relay Output:

Isolated and sealed single pole double throw (SPDT) relay, Form C

Switching Mode:

Selectable, NO or NC states

Max. Relay Switching Voltage:

120 Vdc or 240 Vac

Max. Switched Current: 10 amps

Time Delay: Adjustable from 0.15 to 60 seconds

Strobe Type: Xenotube

Strobe Flash: 1 per second

Max. Temp. Rating: 70°C (158°F)

Sensor Voltage Supply:

13.5 Vdc @ 100 mA

Mounting Connection: ¼" NPT

Conduit Connection: ½" NPT

Enclosure Rating: NEMA-4X (IP65)

Enclosure Material:

Polypropylene (PP), flame retardant

Dimensions: 7.1 Dia. x 16.2 cm High (2.8 x 6.4") x ¼" NPT

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)				
Model No.	Price	Description	Mat'l	Size
FLCN-101	\$235	Level alert single sensor controller	PP	2.8 x 6.4 x ¼" NPT
EE-2675	180	Reference Book: Electrical Engineer's Reference Book		

Comes with complete operator's manual.

Ordering Example: FLCN-101, level alert single sensor controller, \$235.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters