

# NICKEL-PLATED BRASS LUER FITTINGS, ADAPTORS, and MANIFOLDS

OMEGA's new precision-machined adaptors, connectors, and stopcocks can be easily integrated with a variety of assemblies and test apparatus. They are used in industrial and laboratory applications where precision luer-type connectors are required.

## ADAPTORS

**MOST POPULAR MODELS HIGHLIGHTED!**

Provide secure connections and easy disconnect applications for your fluid handling and Luer-fitting needs. Made of nickel-plated 360 brass.

### How to Order Adaptors

Nickel-Plated Brass - Water Tested to 45 psi

Model No.	Price	Description
FT-6156	\$7.00	Hose ends for 1/8" to 3/16" ID tubing to male luer lock
FT-6157	7.00	Hose ends for 1/16" to 3/32" ID tubing to male luer lock
FT-6159	4.00	Hose ends for 1/16" to 3/32" ID tubing to female luer
FT-6168	5.00	Hose ends for 3/16" to 1/4" ID tubing to female luer
FT-6169	6.00	Hose ends for 1/4" to 5/16" ID tubing to male luer needle lock
FT-6170	5.00	Female luer to male luer
FT-6176	9.00	Female luer to male luer lock




## FLUSHING MANIFOLDS

Pressure manifolds make it possible to design a miniature piping system utilizing various luer connections. Flushing manifolds allow liquids to be flushed through needles, catheters, and other components. The manifolds are made of nickel-plated 360 brass.



## PRESSURE MONITORING MANIFOLDS


OMEGA's extensive selection of pressure monitoring manifolds allows users to create their own miniature piping systems utilizing various luer connections. The sturdy metal base with metal luer fittings can be sterilized for repeated, reliable, economical service. All pressure monitoring manifolds are made of nickel-plated 360 brass.



FT-6156



FT-6179



FT-6204



FT-6176

**MOST POPULAR MODELS HIGHLIGHTED!**

### to Order Adaptors (Continued)

Model No.	Price	Description
FT-6178	\$6.00	Male luer lock to closed end
FT-6179	4.00	Female luer lock to closed end
FT-6203	9.00	Female luer to screw cap threaded fitting for 0.082" ID tubing
FT-6204	10.00	Male luer lock to screw cap threaded fitting for 0.042" ID tubing
FT-6132	46.00	Three-way "Y" adaptor - all hose ends for 1/8" to 3/16" ID tubing
FT-6212	5.00	Female luer to 10-32 standard thread

### How to Order Flushing Manifolds

Model No.	Price	Description
FT-6270	\$350	6 male luer locks with 0.750" spacing between locks
FT-6271	361	8 male luer locks with 0.562" spacing between locks
FT-6272	372	10 male luer locks with 0.450" spacing between locks

### How to Order Pressure Monitoring Manifolds

Model No.	Price	Description
FT-6103	114	Pressure monitor - 6 male luer locks

# CHROME-PLATED BRASS LUER STOPCOCKS

These high quality, leakproof luer fittings are manufactured to the ANSI/HIMA MD70.1 standard. Luer stopcocks are made of Type 360 brass and are chrome-plated. These stopcocks are easily integrated into assemblies with other stopcocks, manifolds, adaptors, and glass syringes.

**MOST POPULAR MODELS HIGHLIGHTED!**

## How to Order Stopcocks

One-Way - Chrome-Plated Brass - Water Tested to 80 psi

Model No.	Price	Description
FT-6019	\$36	Female luer to male luer
FT-6021	40	Female luer to male luer lock
FT-6023	44	Male luer lock to male luer lock
FT-6024	50	Hose ends for 1/16" to 3/16" ID tubing
FT-6025	50	Hose ends for 1/8" to 1/2" ID tubing
FT-6026	50	Hose ends for 3/16" to 1/4" ID tubing
FT-6027	50	Hose ends for 1/4" to 3/8" ID tubing
FT-6040	51	Female luer to screw cap threaded fitting for 0.042" ID tubing
FT-6041	51	Female luer to screw cap threaded fitting for 0.067" ID tubing
FT-6042	51	Female luer to screw cap threaded fitting for 0.082" ID tubing
FT-6043	114	Female luer to screw cap threaded fitting for 0.118" ID tubing



## How to Order Stopcocks

Three-Way - Chrome-Plated Brass - Water Tested to 80 psi

Model No.	Price	Description
FT-6001	\$50	Female luer to male luer - right side arm female luer
FT-6011	69	Female luer to male luer lock - right side arm female luer
FT-6014	80	Male luer to male luer lock - right side arm female luer
FT-6015	72	Female luer to male luer - left side arm female luer

# GLASS SYRINGES

These jumbo glass syringes meet the highest standards of accuracy and uniformity and are a staple in laboratory and industrial applications. The body and plunger are made of borosilicate glass for corrosion and heat resistance.

## How to Order Jumbo Glass Syringes

Model No.	Price	Description
FT-5157	\$79	50 CC luer lock tip syringe
FT-5177	271	100 CC luer lock tip syringe
FT-5331	446	150 CC luer lock tip syringe
FT-5333	559	250 CC luer lock tip syringe



L

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters