

LOW COST NEMA 6 (IP68) LIQUID LEVEL SWITCHES

LVN-10
\$29



- ✓ Low Cost Compact Design
- ✓ NEMA 6 (IP68) Rated
- ✓ User Selectable, Normally Open or Normally Closed
- ✓ Mounts Vertically at Top or Bottom of Tank
- ✓ Reed Switch Design for High Repeatability

These liquid level switches are sealed with potting compound. The only path for liquid to the electrical switch would be through the wires. If the wires are terminated in an appropriate manner [e.g. NEMA 6 (IP68) connectors], the level switch will meet or exceed a NEMA 6 (IP68) rating, making them suitable for submersion with years of worry free operation in moisture-laden environments. A sealed SPST switch provides consistent accuracy and high repeatability with the effects of shock, vacuum or vibration minimized. The switch is extremely versatile since it is user selectable as a normally open or normally closed by simply reversing the float or the mounting of the switch. The standard NPT male fittings allow for quick installation in either the top or bottom of the tank or vessel.

SPECIFICATIONS

Stem Material: Brass

Float Material: Buna-N

Wetted Material: Brass, Buna-N, 316SS

Operating Temperature:

-40 to 82°C (-40 to 180°F)

110°C (230°F) in Oil

Maximum Pressure Rating:

LVN-10: 160 psi



LVN-20: 225 psi

Mounting:

LVN-10: 1/8" NPT


LVN-20: 1/4" NPT

Switch: SPST



Switch Actuation: Approximately 1/2 the distance from the end of stem to mounting or halfway point of float travel

Lead Wires: 20 AWG, 24" PVC



Specific Gravity of Float:
LVN-10: 0.56
LVN-20: 0.70

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)				
Model No.	Price	Stem Material	NPT Size	Switch Rating
LVN-10	\$29	Brass	1/8"	50 VA
LVN-20	35	Brass	1/4"	50 VA

Accessory

Model No.	Price	Description
ES-2247	\$125	Reference Book: Urban Water Supply Handbook

Comes complete with operator's manual.

Ordering Examples: LVN-20, low cost liquid level switch, \$35. LVN-10, low cost liquid level switch, \$29.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters