


# OMEGAFLEX® POLYPROPYLENE TUBING



**TYPP-1418-100**

**\$20**  
Basic 100'  
Spool



This is a tough, heat-resistant tubing, ideal for the transfer of hot liquids or gases. It is recommended for low pressure systems and uses where higher temperatures and pressures are encountered. It has good compatibility to acids and alkalies.

**SPECIFICATIONS\***

**Operating Temperature Range:**

-40° to 121°C (-40° to 250°F)

**Durometer, nom. (Shore) 15 secs: 75 (D)**

**Color:** Translucent

**Specific Gravity:** 0.90

**Tensile Strength (psig):** 3700

**Ultimate Elongation:** 200

**Minimum Bend Radius:**

Ten times tube OD

*\* Specifications given are typical and are meant only as a guide. Field testing is required to find the actual operating specifications in a given application.*

**To Order** (Specify Model Number)

**AVAILABLE FOR FAST DELIVERY!**

MODEL NO.	PRICE	STD LENGTH (ft)	WALL (in)	OD (in)	ID (in)	WORKING psi at 70°F	WEIGHT (lbs)
TYPP-1418-100	\$20	100	1/16	1/4	1/8	272	3.0
TYPP-14170-100	20	100	0.04	1/4	0.17	149	1.5
TYPP-516316-100	25	100	1/16	3/8	1/4	196	3.0
TYPP-3814-100	30	100	1/16	3/8	1/4	157	3.1
TYPP-1238-100	32	100	1/16	1/2	3/8	112	5.0
TYPP-5812-100	50	100	1/16	3/4	1/2	87	6.0
TYPP-3458-100	55	100	1/16	3/4	5/8	71	7.0
TYPP-134-100	125	100	1/8	1	3/4	109	13.1
TYPP-1141-100	185	100	1/8	1 1/4	1	87	13.5
TYPP-178-100	110	100	1/16	1	7/8	52	7.3
TYPP-112114-100	210	100	1/8	1 1/2	1 1/4	71	21.3
TYPP-134112-100	250	100	1/8	1 3/4	1 1/2	60	25.2
TYPP-2134-100	285	100	1/8	2	1 3/4	52	29.1

Ordering Example: TYPP-1418-100, 100' of tubing, 1/16" wall, of 1/8" ID x 1/4" OD, \$20.

# omega.co.uk<sup>®</sup>

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

[www.omega.co.uk](http://www.omega.co.uk)



#### UNITED STATES

[www.omega.com](http://www.omega.com)

1-800-TC-OMEGA  
Stamford, CT.

#### UNITED KINGDOM

[www.omega.co.uk](http://www.omega.co.uk)

Manchester, England  
0800-488-488  
+44-(0)161-777-6611

#### CANADA

[www.omega.ca](http://www.omega.ca)

Laval(Quebec)  
1-800-TC-OMEGA

#### FRANCE

[www.omega.fr](http://www.omega.fr)

0800-466-342

#### GERMANY

[www.omega.de](http://www.omega.de)

Deckenfronn, Germany  
0800-8266342

#### BENELUX

[www.omega.nl](http://www.omega.nl)

0800-099-33-44



## More than 100,000 Products Available!

### • Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

### • Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

### • pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

### • Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

### • Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

### • Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters