



HEAT CABLE CONNECTION ACCESSORIES

Junction Box and Controls Enclosure


RTES

\$18



- ✓ Molded Ryton Construction
- ✓ Stainless Steel Hardware
- ✓ NEMA 4X Rated Liquid Tight Design
- ✓ Power Connection or Splice and T Kits


The molded Ryton plastic junction box has outstanding chemical corrosion resistance, superior thermal stability, high strength and rigidity, and is nonflammable.



TYPICAL DIMENSIONS FOR ENCLOSURES

- A.** Strategically placed cable entries allow maximum flexibility for installation (heating cable cut away for clarity)
- B.** Stainless steel tiedown support provides positive attachment to pipes
- C.** Heavy-duty support legs give stable mounting and provide conduit clearance for applications with up to 3" of insulation
- D.** Opening for 20 mm (3/4") conduit hub
- E.** Stainless steel, sheath temperature sensor (type RTAS only)

B



RTES end seal kit, \$18, shown smaller than actual size.

- End seal kit includes:
- 1 end cap
 - 1 pressure plate
 - 1 GRSR self-regulating cable sealing grommet
 - 1 GRCW constant wattage cable sealing grommet

The RTES end seal fitting is a NEMA 4X rated enclosure designed to terminate all OMEGALUX® heating cables. This model provides waterproof cable entry for one cable, enclosure support and a waterproof corrosion resistant enclosure. The fitting has two different curved mounting surfaces. One side has a 1 1/2" radius curved surface which provides a stable support on pipes with a diameter of three inches or more. The other side has a 1/2" radius curved surface which permits a better fit on smaller pipes. In addition, this side also has four "feet", for installation on flat surfaces. Attach the RTES end seal fitting to a pipe using OMEGALUX fiberglass tape (to order, see page B-28).

AVAILABLE FOR FAST DELIVERY!

To Order (Specify Model Number)		
Model No.	Price	Description
RTES	\$18	End seal fitting kit

Ordering Example: RTES, end seal fitting for heating cable, \$18.

omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters