


CONNECTORS

NO SPECIAL TOOLS REQUIRED!

CX136 Series
All Models
\$2.50

- ✓ Heavy-Duty Construction
- ✓ Rated to 105°C (215°F)
- ✓ Solderless Connection
- ✓ 22-26 AWG Wire Size
- ✓ Flame-Retardant Thermoplastic Shells
- ✓ High-Conductivity, Gold-Plated over Nickel-Plated Contacts




 MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

MODEL NO.	PRICE	NO. OF CONTACTS	COMPATIBLE SENSORS*
CX136-3	\$2.50	5	PX141, PX142, PX143, PX161, PX162, PX163, PX164
CX136-4	2.50	4	PX26, PX137, PX138, PX139, PX170, PX185
CX136-8	2.50	8	PX149

* See section B for compatible sensors/transducers.

Ordering Example: CX136-4, connector for PX26 transducer, \$2.50.



OEM STYLE CONNECTORS FOR PX-105 AND PX-106 PRESSURE TRANSDUCERS

- ✓ Durable Valox® Shell
- ✓ Rated to 125°C (257°F)
- ✓ Solder/Crimp Contacts
- ✓ 16-20 AWG Wire Size
- ✓ High-Conductivity, Tin-Plated over Brass Contacts
- ✓ Contacts Included

CX106-4
\$1



 MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

MODEL NO.	PRICE	CONTACT (PINS ONLY)
CX106-4	\$1	3

Ordering Example: PX106-CONNECTOR connector only for PX106 transducer, \$6.
CX106-4, contact pins, package of 3, \$1, pins and connector sold separately.

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
ME-1755	\$150	Reference Book: Practical Guide Pressure Vessel



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

FRANCE

www.omega.fr

0800-466-342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters