

MECHANICAL FORCE GAGES INDUSTRIAL GRADE

DFG81 Series

All Models
\$560

- ✓ ±0.3% Accuracy
- ✓ Rugged Die-Cast Aluminum Housing
- ✓ Tare Ring and Peak Hold
- ✓ Ergonomic Design, Economical Price
- ✓ Mountable to Test Fixtures

The ruggedly constructed DFG81 gages will withstand harsh industrial environments yet remain accurate to ±0.3%. These gages are sold as kits complete with gage, hard carrying case, 5 measuring tips, and a 3-inch extension rod. The ergonomic design makes the DFG81 ideal for handheld use. It can also be mounted on a test fixture.



DFG81-1KG, \$560, shown close to actual size.



DFG81 gages are sold as kits complete with gage, hard carrying case, 5 measuring tips and a 3" extension rod.



MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

| CAPACITY | | | | | | |
|-----------|--------|------------|-----------|------------|---------|-------|
| MODEL NO. | POUNDS | MODEL NO. | KILOGRAMS | MODEL NO. | NEWTONS | PRICE |
| DFG81-2 | 2 | DFG81-1KG | 1 | DFG81-10N | 10 | \$560 |
| DFG81-5 | 5 | DFG81-2KG | 2 | DFG81-20N | 20 | 560 |
| DFG81-10 | 10 | DFG81-3KG | 3 | DFG81-30N | 30 | 560 |
| DFG81-20 | 20 | DFG81-5KG | 5 | DFG81-50N | 50 | 560 |
| — | — | DFG81-10KG | 10 | DFG81-100N | 100 | 560 |
| DFG81-30 | 30 | DFG81-20KG | 20 | DFG81-200N | 200 | 560 |
| DFG81-50 | 50 | DFG81-30KG | 30 | DFG81-300N | 300 | 560 |
| DFG81-100 | 100 | DFG81-50KG | 50 | DFG81-500N | 500 | 560 |

Comes with gage, hard carrying case, 5 measuring tips and 3" extension rod.

Ordering Example: DFG81-10KG, complete kit with 10 kg range digital force gage, \$560.

ACCESSORY

| MODEL NO. | PRICE | DESCRIPTION |
|-----------|-------|--|
| ME-1804 | \$125 | Reference Book: Mechanical Design Handbook |





UNITED STATES

www.omega.com
1-800-TC-OMEGA
Stamford, CT.

CANADA

www.omega.ca
Laval(Quebec)
1-800-TC-OMEGA

GERMANY

www.omega.de
Deckenpfronn, Germany
0800-8266342

UNITED KINGDOM

www.omega.co.uk
Manchester, England
0800-488-488

FRANCE

www.omega.fr
Guyancourt, France
088-466-342

CZECH REPUBLIC

www.omegaeng.cz
Karviná, Czech Republic
596-311-899

BENELUX

www.omega.nl
Amstelveen, NL
0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Glass Bulb Thermometers, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders Relative Humidity Measurement Instruments, RTD Probes, Elements and Assemblies, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples Thermowells and Head and Well Assemblies, Transmitters, Wire

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Auto-Dialers and Alarm Monitoring Systems, Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485 and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Strain Gages, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters