

MECHANICAL FORCE GAGES

LABORATORY GRADE

DFG82 Series

All Models
\$600



- ✓ Outstanding $\pm 0.1\%$ Accuracy
- ✓ Rugged Die-Cast Aluminum Housing
- ✓ Tare Ring and Peak Hold
- ✓ Ergonomic Design

The DFG82 Series laboratory-grade mechanical force gages are durable yet highly accurate, making them ideal for tension and compression quality control measurements. DFG82 gages are sold in kits, complete with meter, hard case, measuring adaptors (flat head, cone, chisel, notched, small hook, large hook, and fork), and extension rod. The ergonomic design is well suited for handheld testing.



DFG82 is sold as a complete kit including a hard case, measuring adaptors (flat head, cone, chisel, notched, small hook, large hook, and fork), and extension rod.



DFG82-100, \$600, shown close to actual size.

MOST POPULAR MODELS HIGHLIGHTED!

To Order (Specify Model Number)

CAPACITY						
MODEL NO.	POUNDS	MODEL NO.	KILOGRAMS	MODEL NO.	NEWTONS	PRICE
DFG82-2	2	DFG82-1KG	1	DFG82-10N	10	\$600
DFG82-5	5	DFG82-2KG	2	DFG82-20N	20	600
DFG82-10	10	DFG82-3KG	3	DFG82-30N	30	600
DFG82-20	20	DFG82-5KG	5	DFG82-50N	50	600
—	—	DFG82-10KG	10	DFG82-100N	100	600
DFG82-30	30	DFG82-20KG	20	DFG82-200N	200	600
DFG82-50	50	DFG82-30KG	30	DFG82-300N	300	600
DFG82-100	100	DFG82-50KG	50	DFG82-500N	500	600

Comes with hard case, measuring adaptors (flat head, cone, chisel, notched, small hook, large hook, and fork), and extension rod.

Ordering Example: DFG82-10, complete kit with 10 lb range digital force gage, \$600.

ACCESSORY

MODEL NO.	PRICE	DESCRIPTION
OP-17	\$15	Reference Book: Measure for Measure



omega.co.uk[®]

Your One-Stop Source for Process Measurement and Control!

Freephone 0800 488 488 | International +44(0) 161 777 6622 | Fax +44(0) 161 777 6622 | Sales@omega.co.uk

www.omega.co.uk



UNITED STATES

www.omega.com

1-800-TC-OMEGA
Stamford, CT.

UNITED KINGDOM

www.omega.co.uk

Manchester, England
0800-488-488
+44-(0)161-777-6611

CANADA

www.omega.ca

Laval(Quebec)
1-800-TC-OMEGA

FRANCE

www.omega.fr

0800-466-342

GERMANY

www.omega.de

Deckenfronn, Germany
0800-8266342

BENELUX

www.omega.nl

0800-099-33-44



More than 100,000 Products Available!

• Temperature

Calibrators, Connectors, General Test and Measurement Instruments, Handheld Instruments for Temperature Measurement, Ice Point References, Indicating Labels, Crayons, Cements and Lacquers, Infrared Temperature Measurement Instruments, Recorders, Relative Humidity Measurement Instruments, PT100 Probes, PT100 Elements, Temperature & Process Meters, Timers and Counters, Temperature and Process Controllers and Power Switching Devices, Thermistor Elements, Probes and Assemblies, Thermocouples, Thermowells and Head and Well Assemblies, Transmitters, Thermocouple Wire, RTD Probes

• Flow and Level

Air Velocity Indicators, Doppler Flowmeters, Level Measurement, Magnetic Flowmeters, Mass Flowmeters, Pitot Tubes, Pumps, Rotameters, Turbine and Paddle Wheel Flowmeters, Ultrasonic Flowmeters, Valves, Variable Area Flowmeters, Vortex Shedding Flowmeters

• pH and Conductivity

Conductivity Instrumentation, Dissolved Oxygen Instrumentation, Environmental Instrumentation, pH Electrodes and Instruments, Water and Soil Analysis Instrumentation

• Data Acquisition

Communication Products and Converters, Data Acquisition and Analysis Software, Data Loggers Plug-in Cards, Signal Conditioners, USB, RS232, RS485, Ethernet and Parallel Port Data Acquisition Systems, Wireless Transmitters and Receivers

• Pressure, Strain and Force

Displacement Transducers, Dynamic Measurement Force Sensors, Instrumentation for Pressure and Strain Measurements, Load Cells, Pressure Gauges, Pressure Reference Section, Pressure Switches, Pressure Transducers, Proximity Transducers, Regulators, Pressure Transmitters, Strain Gauges, Torque Transducers, Valves

• Heaters

Band Heaters, Cartridge Heaters, Circulation Heaters, Comfort Heaters, Controllers, Meters and Switching Devices, Flexible Heaters, General Test and Measurement Instruments, Heater Hook-up Wire, Heating Cable Systems, Immersion Heaters, Process Air and Duct, Heaters, Radiant Heaters, Strip Heaters, Tubular Heaters